

PG 8057 TD [DOS MK HYGIENEplus]

Freestanding fresh water dishwasher

With baskets, for all locations with high hygiene requirements.



- Max. cleaning performance*: 456 plates/h
- Particularly hygienic results – thermal disinfection
- Assured results thanks to high process safety
- Easy and safe handling thanks to automatic dispensing
- First-class results thanks to freshwater wash system

* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002516278597 / Material number: 11422970 / Old Material Number: 61805787EP1

Construction type and design	
Construction type	Freestanding dishwasher, front loader
Range	Professional
Model	Hygieneplus
Wash system	Fresh water front loader
Number of levels	2
Front	Stainless steel
Lid	Stainless Steel
Side panels	Stainless steel
Application	
Suitable for retirement and care homes	•
Suitable for hospitals	•
Suitable for child care facilities	•
Performance data	
Tested virucidal efficacy	•
Circulation pump Qmax in l/min.	390
Shortest programme duration in min.	5
Maximum final rinse temperature in °C	93
Cleaning performance, plates/h	456
Cleaning performance, baskets/h	24
Possible to wash plastic baskets on 2 levels	•
Service life in wash cycles	15000
Controls	
Control system	TouchControl
Programme selection	Touch on MSetal
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Choice of display language	•
Language-neutral operation	•
Standard electrical connection	
Electrical connection	3N AC 400V 50HZ
Heater rating in kW	8.50
Total connected load in kW	8.90
Fuse rating in A	16
Length of mains connection cable in m	1.70
Possible voltage variant 1	
Electrical connection	AC 230V 50HZ
Heater rating in kW	3.00
Total connected load in kW	3.40
Fuse rating in A	16
Water connection/drainage	
Cold water [number]	1
Hot water [number]	1
Required flow pressure in bar	1.00-10.00
Drain pump [DN]	22
Drain pump head height from floor level, max. in c	100
Integrated water softener	•
Maximum water hardness in mmol/l	10.70

PG 8057 TD [DOS MK HYGIENEplus]

Freestanding fresh water dishwasher

With baskets, for all locations with high hygiene requirements.



EAN: 4002516278597 / Material number: 11422970 / Old Material Number: 61805787EP1

Water protection system	Waterproof system
Water consumption per wash cycle in l	8.00
Dimensions and weight	
External dimensions, height in mm	820
External dimensions with lid, height in mm	835
External dimensions, net width in mm	598
External dimensions, net depth in mm	598
External dimensions, gross height in mm	940
External dimensions, gross width in mm	675
External dimensions, gross depth in mm	745
Usable space in wash cabinet, height in mm	559
Usable space in wash cabinet, width in mm	536
Usable space in wash cabinet, depth of upper basket	474
Usable space in wash cabinet, depth of lower basket in mm	516
In-feed height above floor in mm	216
Net weight [kg]	63
Gross weight in kg	69
Maximum floor loading in N	1200
Emissions data	
Emissions – sound pressure at workplace	45 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	57.0
Heat dissipation into the room in MJ/h	1.08
Programmes	
Universal	•
Super short	•
Short	•
Hygiene plus	•
Thermal disinfection (Vario TD)	•
Glasses	•
Cutlery	•
Plastics	•
Intensive	•
Reactivation	•
Drainage	•
Basket design	
1 x O 891 upper basket for cups	•
1 x U 890 lower basket for inserts	•
1 x E 810 insert for dessert plates	•
2 x E 816 inserts for plates	•
2 x E 165 inserts for cutlery	•
Height-adjustable upper basket	•
Features	
Drying	AutoOpen assisted drying
1 combi dispenser in the door for powder cleaning agent and rinsing agent	•
Integrated dispensing pump/dispensing module for liquid cleaning agent	•
Wash cabinet made from high-quality stainless steel	•
In-door salt container	•
AutoClose	•
Perfect GlassCare	•

PG 8057 TD [DOS MK HYGIENEplus]

Freestanding fresh water dishwasher

With baskets, for all locations with high hygiene requirements.



EAN: 4002516278597 / Material number: 11422970 / Old Material Number: 61805787EP1

Aerosol steam condenser	•
Adjustable temperature holding time	•
Adjustable final rinse temperature	•
Adjustable wash temperature	•
Adjustable rinse time	•
Optical interface	•
A wide range of accessories (optional)	•
Connection options	
External dispensing module for rinse aid	•
Standards, certs, symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
VDE	•
Splash-protection IPX1	•
EMC radio suppressed	•
DIN 10512	•
EN 1717	•