

PR 900
Built-in report printer
For printing process protocols.



- Thermal printer with 60 mm paper width
- Can be installed on the outfeed side with two-door models

EAN: 4002516362081 / Material number: 11491220 / Old Material Number: 69247004D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8615	•
PLW 8616	•
Product category	
Conversion kit	•
Process documentation/operating documentation/communication	•
Product properties	
Colour	Black
Dimensions and weight	
External dimensions, net height in mm	950
External dimensions, net width in mm	77
External dimensions, net depth in mm	69
External dimensions, gross height in mm	125
External dimensions, gross width in mm	200
External dimensions, gross depth in mm	1000
Net weight in kg	2.87
Gross weight in kg	3.59