

CM 6560 MilkPerfection  
Countertop coffee machine  
With WiFiConn@ct, high-quality milk container and many speciality coffees.



- Creamy milk froth for a wide range of coffee specialities
- Perfect results and intense coffee flavour – AromaticSystem
- Two coffees at once at the touch of a button – OneTouch for Two
- Convenient cleaning and maintenance programmes
- Communication with the machine could not be easier – WiFi Conn@ct

EAN: 4002516362067 / Material number: 11590240 /  
Old Material Number: 29656003GB

<b>Construction type</b>	
Appliance Colour	Graphite grey (PF)
<b>Construction type and design</b>	
Freestanding bean-to-cup coffee machine	•
<b>Convenience features</b>	
AromaticSystem	•
OneTouch preparation	•
OneTouch for Two preparation	•
DoubleShot	•
Programmable User profiles	8
Aroma-friendly conical grinder	•
Selectable grinder setting	•
Additional coffee types in ground coffee form possible	•
Programmable amount of coffee	•
Programmable amount of water	•
Programmable water temperature	•
Amount of milk can be programmed	•
Programmable amount of milk froth	•
Pre-brewing programmable	•
TeaTimer	•
<b>User convenience</b>	
Networking with Miele@home	•
Display	DirectSensor
PerformanceMode	•
BrilliantLight	•
Expert mode	•
Heated cup rest	•
MultiLingua	•
No. of bean types	1
No. of bean containers	1
Capacity of bean container A in g	300
Bean container capacity, total in g	300
Capacity of water container in l	1.8
Milk container capacity in l	0.7
Capacity of waste container in capsules	10
Drip tray capacity	0.8
Easily accessible containers	•
Programmable standby time	•
Programmable settings	•
<b>Drink specialities</b>	
Selectable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•

CM 6560 MilkPerfection  
 Countertop coffee machine  
 With WiFiConn@ct, high-quality milk container and many speciality coffees.



EAN: 4002516362067 / Material number: 11590240 /  
 Old Material Number: 29656003GB

Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Espresso macchiato, single	•
Espresso macchiato, double	•
Cappuccino italiano, single	•
Cappuccino italiano, double	•
Flat white, single	•
Flat white, double	•
Café au lait, single	•
Café au lait, double	•
Caffè latte, single	•
Caffè latte, double	•
Warm water, single	•
Hot water, single	•
Black tea, single	•
Herbal tea, single	•
Fruit tea, single	•
Green tea, single	•
White tea, single	•
Japanese tea, single	•
Coffee pot	•
<b>Efficiency and sustainability</b>	
Energy-saving eco-mode selectable	•
Power rating in standby mode in W	0.1
Power rating in networked standby in W	0.5
<b>Cleaning and care</b>	
Manual descaling	•
Automatic rinsing of milk pipework with water from the water container	•
Convenient cleaning programmes	•
Automatic rinsing function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•
Programmable water hardness	•
<b>Technical data</b>	
Height-adjustable serving spout in cm	14.0
Height-adjustable serving spout in cm	8.0
Appliance width in mm	251
Appliance height in mm	359
Appliance depth in mm	427
Total rated load in kW	1.45

CM 6560 MilkPerfection  
 Countertop coffee machine  
 With WiFiConn@ct, high-quality milk container and many speciality coffees.



EAN: 4002516362067 / Material number: 11590240 /  
 Old Material Number: 29656003GB

Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Pump pressure in bar	15
Length of supply lead in m	1.4
<b>Accessories included</b>	
Stainless steel milk tube	•
Milk container made of glass	•
Voucher for CJ 1 coffee pot	•
Voucher for 4 x 250 g Black Edition ONE FOR ALL coffee beans	•
Descaling tablets	•
Cleaning tablets	•
Brief operating instructions on rear of unit	•

**Available display languages**

Available display languages through MultiLingua

bahasa malaysia, dansk, deutsch, english, english (AU), english (CA), english (GB), english (US), español, français, français (CA), français (FR), hrvatski, italiano, magyar, nederlands, norsk, polski, portugês, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά, [?][?][?][?][?][?], [?][?], [?][?], [?][?][?][?], [?][?][?], [?][?][?]