


## PFD 101 U

### Built-under dishwasher

For large amounts of crockery in households, office tea rooms and utility areas.



- Wash performance: 13 place settings in just 36 min.\*
- 13 % less energy consumption\*\*
- Everything completely dry – AutoOpen assisted drying
- Intuitive to operate thanks to clear control panel design
- Flexible loading of load items for the best cleaning results

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

\*\* Based on the ECO programme, compared to predecessor.




EAN: 4002516367031 / Material number: 11605630 / Old Material Number: 61010102GB

Construction type and version	
Construction type	Built-under dishwasher
Range	ProfiLine
Wash system	Fresh water front loader
Number of levels	2
Front	Brilliant white
Side panels	Galvanised
Fascia color	CleanSteel
Application	
Suitable for guesthouses	•
Suitable for universities and schools	•
Suitable for offices	•
Suitable for domestic use	•
Suitable for small businesses	•
Suitable for sports clubs	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Circulation pump Qmax in l/min.	75
Shortest programme duration in min.	36
Maximum final rinse temperature in °C	82
Cleaning performance, place settings/cycle	13
Service life in wash cycles	12500
Miele MOVE	
Network-enabled with Miele MOVE	•
Control system	
Control system	Electronic controls
Programme selection	Programme selector buttons
Max. delay start in h	24
Time left display	•
Programmes [number]	8
Programme sequence indicator	•
Choice of display language	•
Check filter indicator	•
Standard electrical connection	
Electrical connection	AC 230V 50HZ
Heater rating in kW	1.90
Total connected load in kW	2.10
Fuse rating in A	13
Length of mains connection cable in m	1.70
Provided with plug	•
Possible voltage variant 1	
Electrical connection	AC 230V 50HZ
Heater rating in kW	6.10
Total connected load in kW	6.30
Fuse rating in A	32
Water connection/drainage	
Cold or hot water [number]	1
Required flow pressure in bar	1.00-10.00

## PFD 101 U

### Built-under dishwasher

For large amounts of crockery in households, office tea rooms and utility areas.




EAN: 4002516367031 / Material number: 11605630 / Old Material Number: 61010102GB

Drain pump [DN]	22
Drain pump head height from floor level, max. in c	100
Integrated water softener	•
Maximum water hardness in mmol/l	6.50
Water protection system	Waterproof system
Length of water inlet hose in cm	150
Length of water drain hose in cm	150
<b>Dimensions and weight</b>	
External dimensions, height in mm	805
External dimensions, net width in mm	598
External dimensions, net depth in mm	570
External dimensions, gross height in mm	960
External dimensions, gross width in mm	670
External dimensions, gross depth in mm	700
Usable space in wash cabinet, height in mm	540
Usable space in wash cabinet, width in mm	510
Usable space in wash cabinet, depth of upper basket	450
Usable space in wash cabinet, depth of lower basket in mm	450
In-feed height above floor in mm	210
Required niche width in mm	600
Net weight [kg]	44
Gross weight in kg	51
Maximum floor load in N/m <sup>2</sup>	1000
<b>Emissions data</b>	
Emissions – sound pressure at workplace	33 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	0.0
<b>Programmes</b>	
Universal	•
Short	•
Hygiene	•
Cold/Pre-wash	•
Glasses	•
Plastics	•
Energy save/Eco	•
Intensive	•
<b>Basket design</b>	
ExtraComfort P baskets	•
Flexible FlexLine basket design	•
FlexCare glass holder [number]	2
FlexCare cup rack [number]	1
Cutlery basket	•
Height-adjustable upper basket	•
<b>Features</b>	
Drying	Extra drying, AutoOpen assisted drying, Active condensation drying
1 combi dispenser in the door for powder cleaning agent and rinsing agent	•
Wash cabinet made from high-quality stai	•
AutoClose	•
EcoFeedback	•

PFD 101 U

Built-under dishwasher

For large amounts of crockery in households, office tea rooms and utility areas.



EAN: 4002516367031 / Material number: 11605630 / Old Material Number: 61010102GB

Brilliant GlassCare	•
Safety lock	•
Adjustable final rinse temperature	•
Optical interface	•
SmartStart	•
FlexiTimer with EcoStart	•
WiFi module	•
<b>Efficiency and sustainability</b>	
Load size of the ECO programme in place settings	13
Energy efficiency class (A–G)	E
Energy consumption of the ECO program per 100 cycles	93
Water consumption of the ECO programme per cycle in l	12.0
Acoustic airborne noise emission class (A–D)	C
Acoustic airborne noise emission in dB(A) re 1 pW	46
Programme running time of the ECO programme in min	250
<b>Connection options</b>	
External dispensing module for liquid detergent	•
<b>Standards, test certificates and symbols</b>	
CE	•
Complies with Machinery Directive 2006/42/EC	•
VDE	•
EMC radio suppressed	•
DIN EN 17735	•
EN 1717	•
UKCA	•