

WED 665 WCS TDos & 8kg
W1 front-loader washing machine:
with TwinDos & Miele@home – smart laundry care at affordable entry-level price.



- Tested for 20 years of perfect laundry care
- Save energy in the best energy efficiency class (A)
- Automatic detergent dispensing at the touch of a button – TwinDos
- Ironing made simple thanks to pre-ironing with steam
- Miele@home – clever networking opens up new possibilities*

* Additional digital offer from Miele & Cie. KG. All smart applications are made possible with the Miele@home system. The range of functions can vary depending on the model and the country.



EAN: 4002516375340 / Material number: 11611990 / Old Material Number: 11ED6651GB

| | |
|--|-------------------------------|
| Construction type | |
| Suitable for stacking | • |
| Side-by-side | • |
| Slot-in | • |
| Can be built-under | • |
| Door hinge | right |
| Model | |
| Product brand | W1 Chrome Edition |
| Front-loader | • |
| Spinning | |
| Max. spin speed | 1400 |
| Rinse hold | • |
| Without spin function | • |
| Design | |
| Appliance colour | Lotus white |
| Control panel colour | Lotus white |
| Door design | Graphite grey PearlFinish |
| Rotary selector colour | Lotus White |
| Control panel version | Straight |
| Control type | Rotary control |
| Display | DirectSensor white, 7 segment |
| Cleaning performance | |
| TwinDos automatic detergent dispensing | • |
| CapDosing portioned dispensing | • |
| Gentle laundry care | |
| Honeycomb drum | • |
| Load in kg | 8.0 |
| User convenience | |
| Networking with Miele@home | • |
| Delay start up to 24 hours | • |
| Time left display | • |
| AutoClean detergent drawer | • |
| AddLoad | • |
| Efficiency and sustainability | |
| Energy efficiency class (A–G) | A |
| Weighted energy consumption per 100 operating cycles for the wash cycle in kWh | 47 |
| Weighted water consumption per cycle in l | 47 |
| Spin efficiency class | B |
| Acoustic airborne noise emission class (spin cycle) | A |
| Sound emissions during spin cycle in dB(A) re 1 pW | 70 |
| Duration of the "ECO 40–60" programme at nominal capacity | 219 |
| Power rating in off mode in W | 0.30 |
| Power rating in networked standby in W | 0.60 |
| Low temperature wash "Cold" and "20 °C" | • |
| Automatic load control | • |
| Flow meter | • |
| Foam sensing | • |
| ProfiEco motor | • |

WED 665 WCS TDos & 8kg

W1 front-loader washing machine:

with TwinDos & Miele@home – smart laundry care at affordable entry-level price.



EAN: 4002516375340 / Material number: 11611990 / Old Material Number: 11ED6651GB

| Wash programmes | |
|---|---------------------|
| Cottons (coloureds) | • |
| Cottons with pre-wash | • |
| Minimum iron | • |
| Delicates | • |
| Shirts | • |
| Woollens (hand-washable) | • |
| Express 20 | • |
| Dark garments / Denim | • |
| Proofing | • |
| Cottons arrow | • |
| Drain / Spin | • |
| ECO 40-60 | • |
| Washing extras | |
| Short | • |
| Pre-ironing with steam | • |
| Quality | |
| Counterweights made of cast iron | • |
| Safety | |
| Water protection system | Watercontrol-System |
| Safety lock | • |
| PIN-Code | • |
| Optical interface | • |
| Technical data | |
| Dimensions in mm (width) | 596 |
| Dimensions in mm (height) | 850 |
| Dimensions in mm (depth) | 636 |
| Appliance depth in mm with opened door | 1054 |
| Appliance depth excluding door (for building-under) in mm | 600 |
| Weight in kg | 89 |
| Total rated load in kW | 2.10-2.40 |
| Voltage in V | 220-240 |
| Fuse rating in A | 13 |
| Frequency in Hz | 50 |
| Length of supply lead in m | 2 |
| Accessories included | |
| UltraPhase 1 + 2 | • |
| Voucher for 5 Miele UltraPhase cartridges | • |

WED 665 WCS TDos & 8kg

W1 front-loader washing machine:

with TwinDos & Miele@home – smart laundry care at affordable entry-level price.



W1 installation drawing, slanted facia or straight facia, measures in mm



W1 drawing, slanted facia or straight facia, measures in mm



W1 drawing, slanted facia or straight facia, measures in mm



W1 drawing, slanted facia or straight facia, measures in mm