

## PWM 916 [EL DV DD SOM]

Professional washing machine, electrically heated, with drain valve and detergent drawer, M Touch Pro Plus freely programmable, for marine use.



- Drum volume 140 l 140 l, maximum load size 16.0 kg 16.0 kg
- Top cleaning & consumption values – innovative Miele technology
- Ideal operation thanks to colour touch display – M Touch Pro Plus
- Simple and safe operation thanks to automatic door lock
- Connected for the future using LAN and WiFi

EAN: 4002516391609 / Material number: 11682960 / Old Material Number: 51916008SOM

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Control panel colour	Stainless steel
Maximum load with a load ratio of 1:9 in kg	16.0
Load ratio	1:9
Load in kg	16.0
Drum volume in l	140
Door opening [Ø] in mm	415
Door opening angle in degrees	180
Door hinge	right
Automatic door lock	•
Innovative suds container	•
Maintenance-free motor with frequency converter	•
Patented honeycomb drum 2.0	•
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	6.20
Specific energy consumption for cold water connection in kWh/kg	0.14
Specific water consumption for hot water connection in l/kg	5.90
Specific energy consumption for hot water connection in kWh/kg	0.06
Water consumption with cold water connection in l	99.2
Water consumption for cold water connection in Mops standard 60 °C programme in l	182.2
Energy consumption with cold water connection in kW	2.24
Energy consumption for cold water connection in Mops standard 60 °C programme in kWh	3.21
Programme duration in minutes with cold water connection	49
Water consumption with hot water connection in l	94.4
Water consumption for hot water connection in Mops standard 60 °C programme in l	178.1
Energy consumption with hot water connection in kW	0.96
Energy consumption for hot water connection in Mops standard 60 °C programme in kWh	1.33
Programme duration in minutes with cold water and hot water connection	43
Water consumption in ECO programme with cold water connection in l	92.8
Energy consumption in ECO programme with cold water	1.60
Programme duration in minutes with cold water connection in ECO programme	34
Water consumption in ECO programme with hot water connection in l	91.2
Energy consumption in ECO programme with hot water	0.48

## PWM 916 [EL DV DD SOM]

Professional washing machine, electrically heated, with drain valve and detergent drawer, M Touch Pro Plus freely programmable, for marine use.



EAN: 4002516391609 / Material number: 11682960 / Old Material Number: 51916008SOM

Programme duration in minutes with cold water and hot water connection in ECO programme	32
Programme running time in minutes for Mops standard 60 °C programme with cold water connection	53
Programme running time in minutes for Mops standard 60 °C programme with hot water connection	47
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	44
Residual moisture when processing cleaning cloths in %	25
Spin speed in rpm	1075
g factor	462
Tested operating hours	30000
<b>Control system</b>	
Control system	M Touch Pro Plus
Programmability	Freely programmable
Max. delay start in h	Freely selectable
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Option to enter weight prior to start of programme	•
<b>Standard/target grp programmes</b>	
Basic programmes	•
<b>Dispensing</b>	
Detergent drawer	3 compartments
Maximum number of connections for liquid dispenser pumps [number]	12
Empty sensor	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	3 AC 400V 50 HZ
Heater rating in kW	14.00
Total connected load in kW	14.60
Fuse rating in A	25
<b>Possible voltage variant 1</b>	
Electrical connection	3 AC 400V 60 HZ
Heater rating in kW	14.00
Total connected load in kW	14.60
Fuse rating in A	25
<b>Water connection/drainage</b>	
Cold water [number]	3 x 1/2" hose w/ 3/4" union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Hard water (optional) [number]	2 x 1/2" w/ 3/4" union
Dump valve	DN 70
<b>Dimensions and weight</b>	
External dimensions, height in mm	1450
External dimensions, width in mm	924
External dimensions, depth in mm	835
External dimensions, gross height in mm	1585
External dimensions, gross width in mm	1090
External dimensions, gross depth in mm	1130
Net weight in kg	347.0

## PWM 916 [EL DV DD SOM]

Professional washing machine, electrically heated, with drain valve and detergent drawer, M Touch Pro Plus freely programmable, for marine use.

EAN: 4002516391609 / Material number: 11682960 / Old Material Number: 51916008SOM

Gross weight in kg	367
Maximum floor load in N/m <sup>2</sup>	5189
<b>Emissions data</b>	
Emission sound pressure level in the workplace	65 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	6.48
<b>Features</b>	
Patented pre-spin	•
Cloth reprocessing	•
3-dimensional imbalance monitoring	•
Disinfection rinse	•
Efficient scoop-and-ladle ribs	•
EcoSpeed	•
Spring-in-spring system	•
Temperature monitoring	•
Special heater element	•
Automatic load control+	•
Volumetric flow meter (optional)	•
Weighing plinth (optional)	•
Add laundry	•
Programme selection via colour frame	•
Emergency switch-off	•
Machine-independent accessories	•
<b>Efficiency and sustainability</b>	
Recycling rate in %	92
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
Water recovery (optional)	•
LAN	•
WiFi	•
Connector Box	•
<b>Capacities</b>	
Respirator masks [number]	13
Helmets [number]	4
Overalls [number]	2
Over jackets [number]	3
Chemical protection suits [number]	1
Synthetic duvets [number]	1
Synthetic pillows [number]	3
Down duvets [number]	1
Down pillows [number]	3
Cloths, 22 g [number]	355
Cotton mops, 40 cm / 190 g [number]	82
Cotton mops, 50 cm / 220 g [number]	71
Microfibre mops, 40 cm / 120 g [number]	130
Microfibre mops, 50 cm / 170 g [number]	91
Mops, office, 100 g [quantity]	160
Mops, stairway, 150 g [quantity]	105
Summer horse blankets [number]	3

## PWM 916 [EL DV DD SOM]

Professional washing machine, electrically heated, with drain valve and detergent drawer, M Touch Pro Plus freely programmable, for marine use.



EAN: 4002516391609 / Material number: 11682960 / Old Material Number: 51916008SOM

Standards, test certificates and symbols	
CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
UKCA	•
WEEE	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•