

## PWM 307 [EL DP-1]

Professional washing machine, Little Giants, electric heating, drain pump and the shortest cycle time of 69 min minutes for high laundry throughput.



- Drum volume 64 l, load capacity 7.0 kg
- Tested for intensive use – unparalleled Miele quality
- 22 % less water consumption and 28 % less energy consumption\*
- M Select control unit with a wide range of standard programmes

- Future-proof networking via WiFi

\* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.



EAN: 4002516413813 / Material number: 11693340 / Old Material Number: 51307172GB

### Construction type and version

Construction type	Front-loader, stackable
Range	Evolution
Front	Lotus white
Load in kg	7.0
Drum volume in l	64
Door opening [Ø] in mm	300
Door opening angle in degrees	167
Door hinge	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated drum rear panel made of stainless steel	•

### Application

Suitable for hotels and restaurants	•
Suitable for residential homes and apartments	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•

### Performance data

Tested virucidal efficacy	•
Specific water consumption for cold water connection in l/kg	7.00
Specific energy consumption for cold water connection in kWh/kg	0.14
Water consumption with cold water connection in l	49.0
Energy consumption with cold water connection in kW	0.98
Programme duration in minutes with cold water connection	69
Residual moisture with cold rinse in %	48
Spin speed in rpm	1600
g factor	704
Tested operating hours	30000

### Control system

Control system	M Select
Programmability	programmable
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Language can be selected easily at any time	•

### Standard/target grp programmes

Basic programmes	•
------------------	---

### Dispensing

Detergent drawer	3 compartments
CapDosing	•

## PWM 307 [EL DP-1]

Professional washing machine, Little Giants, electric heating, drain pump and the shortest cycle time of 69 min minutes for high laundry throughput.



EAN: 4002516413813 / Material number: 11693340 / Old Material Number: 51307172GB

### Standard electrical connection

Heating type	Electric
Electrical connection	230V~ 50HZ
Heater rating in kW	2.30
Total connected load in kW	2.50
Fuse rating in A	13

### Water connection/drainage

Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22

### Dimensions and weight

External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	714
External dimensions, gross height in mm	944
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	768
Net weight in kg	98.0
Gross weight in kg	102
Maximum floor load in N	2820

### Emissions data

Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.00

### Features

3-dimensional imbalance monitoring	•
Commercial shock absorbers	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
Efficient drum rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Flow meter	•
Add laundry	•
Machine-independent accessories	•

### Efficiency and sustainability

Load capacity for the "eco 40–60" program in lbs.	7.0
Energy efficiency class (A–G)	A
Spin efficiency class (A–G)	A
Weighted energy consumption per 100 cycles in the "eco 40–60" program in kWh	45
Weighted water consumption per cycle in the "eco 40–60" program in l	37
Noise emission rating (spin cycle) (A–D)	A
Noise emission during spin cycle in dB(A) re 1 pW	72
Program runtime in the "eco 40–60" program in min	199
Recycling rate in %	95

## PWM 307 [EL DP-1]

Professional washing machine, Little Giants, electric heating, drain pump and the shortest cycle time of 69 min minutes for high laundry throughput.



EAN: 4002516413813 / Material number: 11693340 / Old Material Number: 51307172GB

### Connection options

Payment system (optional)

•

Optical interface for service access

•

WiFiConn@ct

•

### Standards, test certificates and symbols

CE

•

VDE-EMC

•

VDE

•

Splash-proof safety rating IPX4

•

WRAS

•

WEEE

•

Complies with Machinery Directive 2006/42/EC

•