

## PDR 307 [EL]

Professional vented dryer, Little Giants, electrically heated  
with a shortest cycle time of 77 min for a high throughput of laundry.



- Drum volume 130.00 l, load capacity 7.0 kg
- Tested for intensive use – unparalleled Miele quality
- Language-neutral fascia panel with rotary control – M Select
- Precision drying of all standard fabrics – PerfectDry



EAN: 4002516413592 / Material number: 11693550 /  
Old Material Number: 52307372GB

### Construction type and version

|                                |                         |
|--------------------------------|-------------------------|
| Construction type              | Front-loader, stackable |
| Range                          | Evolution               |
| Front                          | Lotus white             |
| Fascia color                   | Stainless steel         |
| Load in kg                     | 7.0                     |
| Drum volume in l               | 130.00                  |
| Drying system                  | Exhaust air             |
| Door opening [Ø] in mm         | 370                     |
| Door opening angle in degrees  | 167                     |
| Door hinge                     | left                    |
| Stainless steel honeycomb drum | Yes                     |

### Application

|   |   |
|---|---|
| Suitable for the hotel and catering industry          | • |
| Suitable for residential homes and apartments         | • |
| Suitable for small businesses                         | • |
| Suitable for universities, nurseries, and schools     | • |
| Suitable for camp sites                               | • |
| Suitable for sports clubs                             | • |
| Suitable for beauty salons, spas, and fitness centres | • |
| Suitable for domestic use                             | • |
| Suitable for amusement parks & holiday complexes      | • |
| Suitable for state/community care facilities          | • |

### Performance data

|  |      |
|--|------|
| Maximum evaporation capacity in l/hour   | 2.60 |
| Specific energy consumption in kWh/kg  | 0.49 |
| Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW | 0.49 |
| Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a | 0.41 |
| Programme duration in min.   | 77   |
| Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes     | 77   |
| Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in | 66   |

### Control system

|   |                              |
|---|------------------------------|
| Control system                                | M Select                     |
| Programmability                               | programmable                 |
| User interface                                | Residual moisture controlled |
| Max. delay start in h                         | 24                           |
| Time left display                             | •                            |
| Programme sequence indicator                  | •                            |
| Control panel with easy-to-understand symbols | •                            |
| Language can be selected easily at any time   | •                            |

### Standard/target grp programmes

|                  |   |
|------------------|---|
| Basic programmes | • |
|------------------|---|

### Standard electrical connection

|              |          |
|--------------|----------|
| Heating type | Electric |
|--------------|----------|

## PDR 307 [EL]

Professional vented dryer, Little Giants, electrically heated  
with a shortest cycle time of 77 min for a high throughput of laundry.



EAN: 4002516413592 / Material number: 11693550 /  
Old Material Number: 52307372GB

|                              |                   |
|------------------------------|-------------------|
| Electrical connection        | 220-230V~ 50/60HZ |
| Electric heater rating in kW | 2.52-2.76         |
| Total connected load in kW   | 2.76-2.99         |
| Fuse rating in A             | 13                |

### Dimensions and weight of dryer

|   |      |
|---|------|
| External dimensions, height in mm       | 850  |
| External dimensions, width in mm        | 596  |
| External dimensions, depth in mm        | 717  |
| External dimensions, gross height in mm | 940  |
| External dimensions, gross width in mm  | 660  |
| External dimensions, gross depth in mm  | 820  |
| Net weight in kg                        | 49.0 |
| Gross weight in kg                      | 55   |
| Maximum floor load in N                 | 920  |

### Emissions data

|  |                     |
|--|---------------------|
| Emission sound pressure level in the workplace | <70 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h         | 0.76                |

### Features

|                                 |   |
|---------------------------------|---|
| Intelligent drum reversal       | • |
| Axial airflow                   | • |
| Large-surface filter            | • |
| PerfectDry                      | • |
| SoftLift drum ribs              | • |
| Low temperature function        | • |
| Drying basket (optional)        | • |
| Drum lighting                   | • |
| Machine-independent accessories | • |

### Efficiency and sustainability

|  |        |
|--|--------|
| Energy efficiency class  | C      |
| Annual energy consumption in kWh   | 524    |
| Noise in dB(a) in the Cottons Normal dry standard programme with a full load | 66     |
| Duration in minutes in the standard programme                                | 95     |
| How it works   | Vented |
| Load in kg   | 7.0    |
| Recycling rate in %  | 95     |

### Connection options

|                                      |   |
|--------------------------------------|---|
| Payment system (optional)            | • |
| Optical interface for service access | • |
| LAN/WiFi module (optional)           | • |
| WiFiConn@ct                          | • |

### Standards, test certificates and symbols

|  |   |
|--|---|
| CE   | • |
| VDE  | • |
| VDE-EMC                                      | • |
| Splash-proof safety rating IPX4              | • |
| WEEE   | • |
| UKCA   | • |
| Complies with Machinery Directive 2006/42/EC | • |

PDR 307 [EL]

Professional vented dryer, Little Giants, electrically heated  
with a shortest cycle time of 77 min for a high throughput of laundry.