

## PDR 514 TOP [EL]

Professional vented dryer, electric heating  
with easy-to-use M Select TOP time control.



- Drum volume 250.00 l , load size 10.0 kg – 14.0 kg
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Connected for the future using LAN and WiFi

EAN: 4002516408598 / Material number: 11717750 / Old Material Number: 52514001EU

Construction type and version	
Construction type	Front loader
Range	Performance
Front	Iron grey
Fascia color	Stainless steel
Load size with a load ratio of 1:25	10.0
Load size with a load ratio of 1:18	14.0
Drum volume in l	250.00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour	13.00
Specific energy consumption in kWh/kg	0.53
Programme duration in min.	24
Service life in drying cycles	40000
Control system	
Control system	M Select Benchmark
Programmability	Setting of defined parameters
User interface	time-controlled
Max. delay start in h	24
Time left display	•
Control panel with easy-to-understand symbols	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3N AC 400V 50/60HZ
Electric heater rating in kW	13.50
Steam heater rating in kW	0.00
Gas heater rating in kW	0.00
Heater rating, hot water in kW	0.00
Total connected load in kW	14.10
Fuse rating in A	25

## PDR 514 TOP [EL]

Professional vented dryer, electric heating  
with easy-to-use M Select TOP time control.



EAN: 4002516408598 / Material number: 11717750 / Old Material Number: 52514001EU

<b>Dimensions and weight of dryer</b>	
External dimensions, height in mm	1400
External dimensions, width in mm	906
External dimensions, depth in mm	852
External dimensions, gross height in mm	1526
External dimensions, gross width in mm	1090
External dimensions, gross depth in mm	938
Net weight in kg	160.4
Gross weight in kg	172
Maximum floor load in N/m <sup>2</sup>	1779
<b>Emissions data</b>	
Emission sound pressure level in the workplace	51 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.90
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
DVGW gas	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•