

PDR 514 ROP [EL]

Professional vented dryer, electric heating

with M Select ROP residual moisture control for perfect drying results.



- Drum volume 250.00 l , load size 10.0 kg – 14.0 kg
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516408642 / Material number: 11717820 / Old Material Number: 52514006EU

| Construction type and version | |
|---|-------------------------------|
| Construction type | Front loader |
| Range | Performance |
| Front | Iron grey |
| Fascia color | Stainless steel |
| Load size with a load ratio of 1:25 | 10.0 |
| Load size with a load ratio of 1:18 | 14.0 |
| Drum volume in l | 250.00 |
| Drying system | Exhaust air |
| Door opening [Ø] in mm | 520 |
| Door opening angle in degrees | 180 |
| Door hinge | left |
| Convertible door hinging | • |
| Stainless steel honeycomb drum | Yes |
| Application | |
| Suitable for the hotel and catering industry | • |
| Suitable for retirement and care homes | • |
| Suitable for facility management | • |
| Suitable for laundrettes | • |
| Suitable for residential homes and apartments | • |
| Suitable for commercial laundries | • |
| Suitable for small businesses | • |
| Suitable for studs, riding schools and stables | • |
| Suitable for universities, nurseries, and schools | • |
| Suitable for hospitals | • |
| Suitable for sports clubs | • |
| Suitable for beauty salons, spas, and fitness centres | • |
| Suitable for amusement parks & holiday complexes | • |
| Suitable for state/community care facilities | • |
| Performance data | |
| Maximum evaporation capacity in l/hour | 13.00 |
| Specific energy consumption in kWh/kg | 0.53 |
| Programme duration in min. | 24 |
| Service life in drying cycles | 40000 |
| Control system | |
| Control system | M Select Benchmark |
| Programmability | Setting of defined parameters |
| User interface | Residual moisture controlled |
| Max. delay start in h | 24 |
| Time left display | • |
| Control panel with easy-to-understand symbols | • |
| Standard electrical connection | |
| Heating type | Electric |
| Electrical connection | 3N AC 400V 50/60HZ |
| Electric heater rating in kW | 13.50 |
| Total connected load in kW | 14.10 |
| Fuse rating in A | 25 |

PDR 514 ROP [EL]

Professional vented dryer, electric heating

with M Select ROP residual moisture control for perfect drying results.



EAN: 4002516408642 / Material number: 11717820 / Old Material Number: 52514006EU

| Possible voltage variant 1 | |
|---|--------------------|
| Electrical connection | 3N AC 400V 60HZ |
| Heater rating in kW | 27.00 |
| Total connected load in kW | 28.20 |
| Fuse rating in A | 50 |
| Dimensions and weight of dryer | |
| External dimensions, height in mm | 1400 |
| External dimensions, width in mm | 906 |
| External dimensions, depth in mm | 852 |
| External dimensions, gross height in mm | 1526 |
| External dimensions, gross width in mm | 1090 |
| External dimensions, gross depth in mm | 938 |
| Net weight in kg | 160.4 |
| Gross weight in kg | 172 |
| Maximum floor load in N/m ² | 1779 |
| Emissions data | |
| Emission sound pressure level in the workplace | 51 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h | 3.90 |
| Features | |
| Intelligent drum reversal | • |
| Axial airflow | • |
| Large-surface fluff filter | • |
| PerfectDry | • |
| SoftLift drum ribs | • |
| AirRecycling | • |
| Communication slot | • |
| Emergency switch-off | • |
| Machine-independent accessories | • |
| Connection options | |
| Payment system (optional) | • |
| Optical interface for service access | • |
| Peak load cut-out/energy management (optional) | • |
| WiFi tumble dryer | • |
| Connector Box | • |
| LAN module (optional) | • |
| Standards, test certificates and symbols | |
| CE | • |
| VDE | • |
| VDE-EMC | • |
| Splash-proof safety rating IPX4 | • |
| WEEE | • |
| UKCA | • |
| Complies with Machinery Directive 2006/42/EC | • |