

PDR 914 [G]

Professional vented dryer, gas heating
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 250.00 l , load size 10.0 kg – 14.0 kg
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516408727 / Material number: 11717900 / Old Material Number: 52914005EU

| Construction type and version | |
|---|------------------------------|
| Construction type | Front loader |
| Range | Performance Plus |
| Front | Iron grey |
| Load size with a load ratio of 1:25 | 10.0 |
| Load size with a load ratio of 1:18 | 14.0 |
| Drum volume in l | 250.00 |
| Drying system | Exhaust air |
| Door opening [Ø] in mm | 520 |
| Door opening angle in degrees | 180 |
| Door hinge | left |
| Convertible door hinging | • |
| Stainless steel honeycomb drum | Yes |
| Application | |
| Suitable for the hotel and catering industry | • |
| Suitable for retirement and care homes | • |
| Suitable for facility management | • |
| Suitable for laundrettes | • |
| Suitable for residential homes and apartments | • |
| Suitable for dry cleaners | • |
| Suitable for commercial laundries | • |
| Suitable for fire brigades and rescue services | • |
| Suitable for studs, riding schools and stables | • |
| Suitable for universities, nurseries, and schools | • |
| Suitable for hospitals | • |
| Suitable for sports clubs | • |
| Suitable for beauty salons, spas, and fitness centres | • |
| Suitable for doctors' and dentists' practices | • |
| Suitable for the petrochemicals industry | • |
| Suitable for the food-processing industry | • |
| Suitable for amusement parks & holiday complexes | • |
| Suitable for state/community care facilities | • |
| Performance data | |
| Maximum evaporation capacity in l/hour | 14.00 |
| Specific energy consumption in kWh/kg | 0.55 |
| Programme duration in min. | 23 |
| Service life in drying cycles | 40000 |
| Control system | |
| Control system | M Touch Pro |
| Programmability | programmable |
| User interface | Residual moisture controlled |
| Max. delay start in h | 24 |
| Time left display | • |
| Programme sequence indicator | • |
| Selectable display languages | • |
| Standard electrical connection | |
| Heating type | Gas |
| Electrical connection | 1N AC 230V 50HZ |
| Electric heater rating in kW | 0.00 |

PDR 914 [G]

Professional vented dryer, gas heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516408727 / Material number: 11717900 / Old Material Number: 52914005EU

| | |
|---|--------------------|
| Gas heater rating in kW | 15.00 |
| Total connected load in kW | 0.60 |
| Fuse rating in A | 10 |
| Dimensions and weight of dryer | |
| External dimensions, height in mm | 1400 |
| External dimensions, width in mm | 906 |
| External dimensions, depth in mm | 852 |
| External dimensions, gross height in mm | 1526 |
| External dimensions, gross width in mm | 1090 |
| External dimensions, gross depth in mm | 938 |
| Net weight in kg | 162.4 |
| Gross weight in kg | 174 |
| Maximum floor load in N/m ² | 1799 |
| Emissions data | |
| Emission sound pressure level in the workplace | 51 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h | 3.90 |
| Features | |
| Intelligent drum reversal | • |
| Axial airflow | • |
| Large-surface fluff filter | • |
| PerfectDry | • |
| SoftLift drum ribs | • |
| AirRecycling | • |
| Communication slot | • |
| Emergency switch-off | • |
| Machine-independent accessories | • |
| Connection options | |
| Payment system (optional) | • |
| Optical interface for service access | • |
| Peak load cut-out/energy management (optional) | • |
| WiFi tumble dryer | • |
| Connector Box | • |
| LAN module (optional) | • |
| Capacities | |
| Respirator masks [number] | 8 |
| Overalls [number] | 1 |
| Over jackets [number] | 2 |
| Synthetic duvets [number] | 1 |
| Synthetic pillows [number] | 2 |
| Down duvets [number] | 1 |
| Down pillows [number] | 2 |
| Cloths, 22 g [number] | 255 |
| Cotton mops, 40 cm [number] | 53 |
| Cotton mops, 50 cm [number] | 45 |
| Microfibre mops, 40 cm [number] | 83 |
| Microfibre mops, 50 cm [number] | 59 |
| Summer horse blankets [number] | 2 |
| Standards, test certificates and symbols | |
| CE | • |
| VDE | • |
| VDE-EMC | • |

PDR 914 [G]

Professional vented dryer, gas heating
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516408727 / Material number: 11717900 / Old Material Number: 52914005EU

Splash-proof safety rating IPX4

DVGW gas

WEEE

UKCA

Complies with Machinery Directive 2006/42/EC

•

•

•

•

•