

## PDR 922 [G]

Professional vented dryer, gas heating  
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 400.00 l, load size 16.0 kg – 22.0 kg
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516409366 / Material number: 11718590 /  
Old Material Number: 52922003EU

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Iron grey
Load size with a load ratio of 1:25	16.0
Load size with a load ratio of 1:18	22.0
Drum volume in l	400.00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for laundrettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour	21.70
Specific energy consumption in kWh/kg	0.53
Programme duration in min.	25
Service life in drying cycles	40000
Control system	
Control system	M Touch Pro
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard electrical connection	
Heating type	Gas

## PDR 922 [G]

Professional vented dryer, gas heating  
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516409366 / Material number: 11718590 /  
Old Material Number: 52922003EU

Electrical connection	1N AC 230V 50HZ
Gas heater rating in kW	21.50
Total connected load in kW	1.00
Fuse rating in A	10

### Dimensions and weight of dryer

External dimensions, height in mm	1400
External dimensions, width in mm	906
External dimensions, depth in mm	1162
External dimensions, gross height in mm	1526
External dimensions, gross width in mm	1090
External dimensions, gross depth in mm	1254
Net weight in kg	203.9
Gross weight in kg	218
Maximum floor load in N	2324

### Emissions data

Emission sound pressure level in the workplace	62 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	2.60

### Features

Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•

### Connection options

Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
WiFi	•
Connector Box	•
LAN module (optional)	•

### Capacities

Respirator masks [number]	16
Overalls [number]	3
Over jackets [number]	5
Synthetic duvets [number]	2
Synthetic pillows [number]	3
Down duvets [number]	2
Down pillows [number]	4
Cloths, 22 g [number]	364
Cotton mops, 40 cm [number]	84
Cotton mops, 50 cm [number]	73
Microfibre mops, 40 cm [number]	133
Microfibre mops, 50 cm [number]	94
Summer horse blankets [number]	3

PDR 922 [G]

Professional vented dryer, gas heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516409366 / Material number: 11718590 /

Old Material Number: 52922003EU

Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
DVGW gas	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•