

K 7763 E

Built-in refrigerator

DailyFresh, FlexiLight 2.0 and DynaCool for more convenience and flexibility.



- Spacious drawer with moisture control – DailyFresh
- Individually adjustable glass shelf lighting with FlexiLight 2.0
- Uniform temperature distribution inside the appliance – DynaCool
- Door shelf heights can be adjusted individually
- Dishwasher-proof door shelves – ComfortClean



EAN: 4002516413097 / Material number: 11729590 / Old Material Number: 36776300GB

<b>Appliance category</b>	
Refrigerator	•
<b>Construction type</b>	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
<b>Design</b>	
Refrigeration section lighting	FlexiLight 2.0
Fan lighting	•
<b>User convenience</b>	
Networking with Miele@home	•
Freshness system	DailyFresh
Fine adjustment inner door	•
ComfortClean	•
DynaCool	•
ComfortSize	•
SoftClose	•
<b>Controls</b>	
Operating concept	FreshTouch
Fridge compartment can be switched off	No
Independent temperature regulation of fridge and freezer zones	No
Automatic SuperCool	•
No. of temperature zones	1
Sabbath mode	•
Party mode	•
Holiday mode	•
<b>Fridge/Fridge section</b>	
No. of shelves	7
of which illuminated	4
Chrome-plated metal bottle rack	•
No. of crisper drawers	2
Number of inner door racks for tinned food	3
Door rack for bottles	2
Door shelves	5
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	E
Annual energy consumption in kWh	114.60
Energy consumption in 24 h in kWh	0.31
<b>Safety</b>	
Lock function	•
Acoustic door alarm	•
Optical door alarm	•
<b>Technical data</b>	
Niche width in mm min.	560
Niche width in mm max.	570
Niche height in mm min.	1772
Niche height in mm max.	1788
Niche depth in mm	550

K 7763 E

Built-in refrigerator

DailyFresh, FlexiLight 2.0 and DynaCool for more convenience and flexibility.




EAN: 4002516413097 / Material number: 11729590 / Old Material Number: 36776300GB

Appliance width in mm	559
Appliance height in mm	1770
Appliance depth in mm	546
Weight in kg	58.6
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	26
Climate class	SN-ST
Refrigerator compartment in l	311
4* freezer compartment in l	0
Total usable capacity in l	311
Noise class (A–D)	B
Sound power in dB(A) re 1 pW	35
Current consumption (mA)	1200
Voltage in V	220-240
Fuse rating in A	13
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2.2
Replacing lamps	Customer Service
<b>Accessories supplied</b>	
Egg tray	•

## K 7763 E

### Built-in refrigerator

DailyFresh, FlexiLight 2.0 and DynaCool for more convenience and flexibility.



K7733E, K7763E, K7732E, K7734F, K7764E, K7743E, K7743D, K7744E, K7773D, K7774D (footnote\*) (installation drawings)

\*1. View from the front, 2. Mains connection cable, L = 2100 mm, 3. Ventilation cut-out min. 200 cm<sup>2</sup>, 4. Ventilation, 5. No connections permitted in this area

K7733E, K7763E, K7732E, K7734F, K7764E, K7743E, K7743D, K7744E, K7773D, K7774D, built-in (footnote\*) (drawings)

\*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher.

K7733E, K7763E, K7732E, K7734F, K7764E, K7743E, K7743D, K7744E, K7773D, K7774D, side view (installation drawings)