

APWM 057
Suction lance
for the use of 20 l canisters.



- Suitable for use with Miele Professional dispenser pumps
- For connecting to up to three washing machines

EAN: 4002516588764 / Material number: 11733620 / Old Material Number: 59510057D

Product category	
Washing machines	•
Machine/accessory category	
PW 413	•
PW 418	•
PW 5082	•
PW 5084 MOPSTAR 80	•
PW 5104 MOPSTAR 100	•
PW 5105 Vario	•
PW 6080	•
PW 6088	•
PW 6163	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PWT 6089	•
PWM 500-08	•
PWM 500-09	•
PWM 506 Mop Star 60	•
PWM 507	•
PWM 508 Mop Star 80	•
PWM 509	•
PWM 900-09	•
PWM 906	•
PWM 907	•
PWM 908	•
PWM 511	•
PWM 909	•
PWM 514	•
PWM 520	•
PWM 912	•
PWM 916	•
PWM 920	•
PDW 909	•
Product category	
Dispenser system	•
Product properties	
Material	Plastic
Colour	Black/white
ProCare canister height incl. suction lance	540
Dimensions and weight	
External dimensions, net height in mm	90
External dimensions, net width in mm	90
External dimensions, net depth in mm	550

APWM 057
Suction lance
for the use of 20 l canisters.



EAN: 4002516588764 / Material number: 11733620 / Old Material Number: 59510057D

External dimensions, gross height in mm	93
External dimensions, gross width in mm	95
External dimensions, gross depth in mm	565
Diameter in mm	45
Net weight [kg]	0.52
Gross weight in kg	0.64