

## PT 8303 SL [PTB Plus EL IGS]

Vented dryer, iron grey sides, electric

In SlimLine design, with residual moisture controls for perfect drying results.



- Drum volume 300.00 l / 300.00 l, load capacity 15.0 kg
- Very easy installation – only 711 mm wide
- Easy to move – direct access underneath
- Shortest cycles thanks to diagonal air flow
- Precision drying of all fabrics – PerfectDry

EAN: 4002516431343 / Material number: 11772730 / Old Material Number: 52830302D

| <b>Construction type and design</b>                   |                               |
|---|-------------------------------|
| Construction type                                     | SlimLine                      |
| Range   | Professional                  |
| Front   | Iron grey                     |
| Load in kg  | 15.0                          |
| Load size with a load ratio of 1:25                   | 12.0                          |
| Load size with a load ratio of 1:20                   | 15.0                          |
| Drum volume in l                                      | 300.00                        |
| Drying system   | Exhaust air                   |
| Door opening [Ø] in mm                                | 520                           |
| Door opening angle in degrees                         | 180                           |
| Door hinge  | left                          |
| Stainless steel drum                                  | •                             |
| Stainless steel honeycomb drum                        | No                            |
| <b>Application</b>                                    |                               |
| Suitable for the hotel and catering industry          | •                             |
| Suitable for retirement and care homes                | •                             |
| Suitable for facility management                      | •                             |
| Suitable for commercial laundries                     | •                             |
| Suitable for universities, nurseries, and schools     | •                             |
| Suitable for hospitals                                | •                             |
| Suitable for sports clubs                             | •                             |
| Suitable for beauty salons, spas, and fitness centres | •                             |
| <b>Performance data</b>                               |                               |
| Maximum evaporation capacity in l/hour                | 11.50                         |
| Specific energy consumption in kWh/kg                 | 0.59                          |
| Programme duration in min.                            | 33                            |
| <b>Controls</b>                                       |                               |
| Control system  | Profitronic B Plus            |
| Programmability                                       | Setting of defined parameters |
| User interface  | Residual moisture controlled  |
| Time left display                                     | •                             |
| Programme sequence indicator                          | •                             |
| Fascia panel with plain text                          | •                             |
| Selectable display languages                          | •                             |
| <b>Standard/target grp programmes</b>                 |                               |
| Basic programmes                                      | •                             |
| <b>Standard electrical connection</b>                 |                               |
| Heating type  | Electric                      |
| Electrical connection                                 | 3N AC 380-415V 50HZ           |
| Electric heater rating in kW                          | 12.20-14.50                   |
| Total connected load in kW                            | 13.60-15.20                   |
| Fuse rating in A                                      | 25                            |
| <b>Dimensions and weight</b>                          |                               |
| External dimensions, height in mm                     | 1800                          |
| External dimensions, width in mm                      | 711                           |
| External dimensions, depth in mm                      | 1089                          |
| External dimensions, gross height in mm               | 1810                          |

## PT 8303 SL [PTB Plus EL IGS]

Vented dryer, iron grey sides, electric

In SlimLine design, with residual moisture controls for perfect drying results.



EAN: 4002516431343 / Material number: 11772730 / Old Material Number: 52830302D

|  |                     |
|--|---------------------|
| External dimensions, gross width in mm         | 800                 |
| External dimensions, gross depth in mm         | 1180                |
| Net weight in kg                               | 139.0               |
| Gross weight in kg                             | 159                 |
| Maximum floor loading in N                     | 1584                |
| <b>Emissions data</b>                          |                     |
| Emission sound pressure level in the workplace | <70 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h         | 1.70                |
| <b>Features</b>                                |                     |
| Intelligent drum reversal                      | •                   |
| Large-surface fluff filter                     | •                   |
| PerfectDry                                     | •                   |
| SoftLift drum ribs                             | •                   |
| Low temperature function                       | •                   |
| Retractable plinth                             | •                   |
| Machine-independent accessories                | •                   |
| <b>Connection options</b>                      |                     |
| Payment system (optional)                      | •                   |
| Serial interface RS 232 (optional)             | •                   |
| Optical interface for service access           | •                   |
| Peak load cut-out/energy management (optional) | •                   |
| <b>Standards, certs, symbols</b>               |                     |
| CE   | •                   |
| VDE  | •                   |
| Splash-proof safety rating IPX4                | •                   |
| WEEE   | •                   |
| Complies with Machinery Directive 2006/42/EC   | •                   |