

PDR 928 [G]

Professional vented dryer, gas heating
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 500.00 l , load size 20.0 kg – 28.0 kg
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516443551 / Material number: 11795800 / Old Material Number: 52928006EU

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Load size with a load ratio of 1:25	20.0
Load size with a load ratio of 1:18	28.0
Drum volume in l	500.00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour	29.60
Specific energy consumption in kWh/kg	0.51
Programme duration in min.	23
Service life in drying cycles	40000
Control system	
Control system	M Touch Pro
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard electrical connection	
Heating type	Gas
Electrical connection	1N AC 230V 50HZ
Electric heater rating in kW	0.00
Gas heater rating in kW	30.00
Total connected load in kW	1.20

PDR 928 [G]

Professional vented dryer, gas heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516443551 / Material number: 11795800 / Old Material Number: 52928006EU

Fuse rating in A	10
Dimensions and weight of dryer	
External dimensions, height in mm	1640
External dimensions, width in mm	1206
External dimensions, depth in mm	1019
External dimensions, gross height in mm	1766
External dimensions, gross width in mm	1390
External dimensions, gross depth in mm	1108
Net weight in kg	246.3
Gross weight in kg	261
Maximum floor load in N/m ²	2828
Emissions data	
Emission sound pressure level in the workplace	58 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.30
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Respirator masks [number]	12
Overalls [number]	3
Over jackets [number]	5
Synthetic duvets [number]	2
Synthetic pillows [number]	5
Down duvets [number]	2
Down pillows [number]	5
Cloths, 22 g [number]	545
Cotton mops, 40 cm [number]	105
Cotton mops, 50 cm [number]	91
Microfibre mops, 40 cm [number]	167
Microfibre mops, 50 cm [number]	118
Summer horse blankets [number]	3
Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
DVGW gas	•

PDR 928 [G]

Professional vented dryer, gas heating
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516443551 / Material number: 11795800 / Old Material Number: 52928006EU

WEEE

UKCA

Complies with Machinery Directive 2006/42/EC

•

•

•