

PDR 914 [EL SOM]

Vented dryer, electrically heated with programmable M Touch Pro controls, for marine applications.



- Drum volume 250.00 l , load size 10.0 kg – 14.0 kg 14.0 kg
- Unique, gentle fabric care – honeycomb drum
- Maximum energy efficiency thanks to Air Recycling Flex
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516471509 / Material number: 11895080 / Old Material Number: 52914002SOM

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Load size with a load ratio of 1:25	10.0
Load size with a load ratio of 1:18	14.0
Drum volume in l	250.00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Convertible door hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for offshore use	•
Suitable for marine use	•
Performance data	
Maximum evaporation capacity in l/hour	13.30
Specific energy consumption in kWh/kg	0.51
Programme duration in min.	24
Service life in drying cycles	40000
Control system	
Control system	M Touch Pro
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3N AC 400V 50/60HZ
Electric heater rating in kW	13.50
Total connected load in kW	14.10
Fuse rating in A	25
Dimensions and weight of dryer	
External dimensions, height in mm	1400
External dimensions, width in mm	906
External dimensions, depth in mm	852
External dimensions, gross height in mm	1526
External dimensions, gross width in mm	1090
External dimensions, gross depth in mm	938
Net weight in kg	160.4
Gross weight in kg	172
Maximum floor load in N/m ²	1779
Emissions data	
Emission sound pressure level in the workplace	51 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.90

PDR 914 [EL SOM]

Vented dryer, electrically heated
with programmable M Touch Pro controls, for marine applications.



EAN: 4002516471509 / Material number: 11895080 / Old Material Number: 52914002SOM

Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling Flex	•
Communication slot	•
Emergency switch-off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Respirator masks [number]	8
Overalls [number]	1
Over jackets [number]	2
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Down duvets [number]	1
Down pillows [number]	2
Cloths, 22 g [number]	255
Cotton mops, 40 cm [number]	53
Cotton mops, 50 cm [number]	45
Microfibre mops, 40 cm [number]	83
Summer horse blankets [number]	2
Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•