

APWM 017

Dispenser pump rack

with slanted base for the complete residual emptying of liquid media containers.

EAN: 4002516501404 / Material number: 11933700 / Old Material Number: 59510017EU



- Suitable for the installation of the dispenser pump casing DOS G2
- Suitable for the installation of the dispenser pump unit DOS GP3
- With four swivel castors for maximum mobility
- Suitable for installing Brightwell dispensing pumps and APWM 054

Product classification	
Washing machines	•
Machine/accessory category	
PW 413	•
PW 413 Mop Star 130	•
PW 418	•
PW 5064	•
PW 5062	•
PW 5055	•
PW 5065	•
PW 5064 MOPSTAR 60	•
PW 5070	•
PW 5082	•
PW 5084 MOPSTAR 80	•
PW 5104 MOPSTAR 100	•
PW 5105 Vario	•
PW 5134 MOPSTAR 130	•
PW 6055	•
PW 6065	•
PW 6055 Vario	•
PW 6065 Vario	•
PW 6065 Plus	•
PW 6068 Plus	•
PW 6080	•
PW 6088	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PW 9055	•
PW 9065	•
PWT 6089	•
PWM 500-08	•
PWM 500-09	•
PWM 506 Mop Star 60	•
PWM 507	•
PWM 508 Mop Star 80	•
PWM 900-09	•
PWM 906	•
PWM 907	•
PWM 908	•

APWM 017

Dispenser pump rack

with slanted base for the complete residual emptying of liquid media containers.

EAN: 4002516501404 / Material number: 11933700 / Old Material Number: 59510017EU



PWM 511	•
PWM 909	•
PWM 514	•
PWM 520	•
PWM 912	•
PWM 916	•
PWM 920	•
PDW 909	•
Product category	
Dispenser system	•
Product properties	
Electrical connection	OHNE
Dimensions and weight	
External dimensions, net height in mm	1030
External dimensions, net width in mm	1000
External dimensions, net depth in mm	371
External dimensions, gross height in mm	1152
External dimensions, gross width in mm	1300
External dimensions, gross depth in mm	413
Net weight [kg]	9.00
Gross weight in kg	10.00