

APLW 869
Battery
for use in ATT 86.



- Recharging time 5 hours
- Charger APLW 868 is sold separately.
- Charging capacity: 2.9 Ah

EAN: 4002516562016 / Material number: 11936210 / Old Material Number: 69686900D

Product classification	
Large-capacity washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
PLW 8615	•
PLW 8616	•
PLW 8617	•
Product category	
Storage/transport system	•
Product properties	
Material	Plastic
Colour	Blue, Grey
Dimensions and weight	
External dimensions, net height in mm	239
External dimensions, net width in mm	117
External dimensions, net depth in mm	75
External dimensions, gross height in mm	125
External dimensions, gross width in mm	165
External dimensions, gross depth in mm	350
Net weight in kg	2.85
Gross weight in kg	3.01
Standards, certs, symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
RoHS Directive	•
Splash protection IPX1	•
Splash protection IPX5	•
GS	•
TÜV	•
Complies with Machinery Directive 2006/42/EC	•