

## PWM 508 [EL DP-1]

Professional washing machine, Little Giants, electric heating, drain pump and target group specific programmes. Capacity 8.0 kg in 59 min.



- Drum volume 73 l, load capacity 8.0 kg
- 22 % less water consumption and 28 % less energy consumption\*
- Tested for intensive use – unparalleled Miele quality
- Language-neutral fascia panel with rotary control – M Select
- Thorough cleaning with professional wash programmes

\* Based on the Coloured items 60 °C programme with a warm water connection, compared to predecessor.



EAN: 4002516532903 / Material number: 11944640 /  
Old Material Number: 51508153GB

Construction type and version	
Construction type	Front-loader, stackable
Range	Performance
Front	Lotus white
Control panel colour	Stainless steel
Load in kg	8.0
Drum volume in l	73
Door opening [Ø] in mm	300
Door opening angle in degrees	167
Door hinge	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated drum rear panel made of stainless steel	•
Application	
Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for residential homes and apartments	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	6.40
Specific energy consumption for cold water connection in kWh/kg	0.13
Specific water consumption for hot water connection in l/kg	6.00
Specific energy consumption for hot water connection in kWh/kg	0.06
Water consumption with cold water connection in l	51.0
Energy consumption with cold water connection in kW	1.05
Programme duration in minutes with cold water connection	69
Water consumption with hot water connection in l	48.0
Energy consumption with hot water connection in kW	0.50
Programme duration in minutes with cold water and hot water connection	59
Residual moisture with cold rinse in %	48

## PWM 508 [EL DP-1]

Professional washing machine, Little Giants, electric heating, drain pump and target group specific programmes. Capacity 8.0 kg in 59 min.



EAN: 4002516532903 / Material number: 11944640 /  
Old Material Number: 51508153GB

Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g factor	704
Tested operating hours	30000
<b>Control system</b>	
Control system	M Select
Programmability	programmable
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Language can be selected easily at any time	•
<b>Dispensing</b>	
Detergent drawer	3 compartments
CapDosing	•
Flexible dispensing adapter (optional)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	230V~
Heater rating in kW	2.65
Total connected load in kW	2.85
Fuse rating in A	13
<b>Possible voltage variant 1</b>	
Electrical connection	2N~ 400V 50HZ
Heater rating in kW	5.30
Total connected load in kW	5.50
Fuse rating in A	13
<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22
<b>Dimensions and weight</b>	
External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	714
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	768
Net weight in kg	103.0
Gross weight in kg	107
Maximum floor load in N	2820
<b>Emissions data</b>	
Emission sound pressure level in the workplace	≤70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.00

## PWM 508 [EL DP-1]

Professional washing machine, Little Giants, electric heating, drain pump and target group specific programmes. Capacity 8.0 kg in 59 min.



EAN: 4002516532903 / Material number: 11944640 /  
Old Material Number: 51508153GB

### Features

3-dimensional imbalance monitoring	•
Commercial shock absorbers	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
Pre-ironing	•
Efficient drum rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•
Machine-independent accessories	•

### Efficiency and sustainability

Load capacity for the "eco 40-60" program in lbs.	8.0
Energy efficiency class (A-G)	A
Spin efficiency class (A-G)	A
Weighted energy consumption per 100 cycles in the "eco 40-60" program in kWh	47
Weighted water consumption per cycle in the "eco 40-60" program in l	47
Noise emission rating (spin cycle) (A-D)	A
Noise emission during spin cycle in dB(A) re 1 pW	72
Program runtime in the "eco 40-60" program in min	219
Recycling rate in %	95

### Connection options

Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
WiFi	•
LAN module (optional)	•
WiFiConn@ct	•

### Standards, test certificates and symbols

CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
WRAS	•
UKCA	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•