

## PDR 508 [EL]

Professional vented dryer, Little Giants, electrically heated with extremely short programme running times. Capacity 8.0 kg 8.0 kg in 84 min minutes.



- Drum volume 130.00 l 130.00 l, load capacity 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Language-neutral fascia panel with rotary control – M Select
- Precision drying of all fabrics – PerfectDry

C

EAN: 4002516527985 / Material number: 11945020 / Old Material Number: 52508353GB

Construction type and version	
Construction type	Front-loader, stackable
Range	Performance
Front	Lotus white
Fascia color	Stainless steel
Load in kg	8.0
Drum volume in l	130.00
Drying system	Exhaust air
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour	2.60
Specific energy consumption in kWh/kg	0.49
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.49
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.41
Programme duration in min.	84
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	84
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	71
Control system	
Control system	M Select
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•

## PDR 508 [EL]

Professional vented dryer, Little Giants, electrically heated with extremely short programme running times. Capacity 8.0 kg 8.0 kg in 84 min minutes.



EAN: 4002516527985 / Material number: 11945020 / Old Material Number: 52508353GB

Language can be selected easily at any time

•

### Standard electrical connection

Heating type	Electric
Electrical connection	230V~ 50/60HZ
Electric heater rating in kW	2.76
Total connected load in kW	2.99
Fuse rating in A	13

### Dimensions and weight of dryer

External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	717
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	49.0
Gross weight in kg	55
Maximum floor load in N/m <sup>2</sup>	920

### Emissions data

Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	0.76

### Features

Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•

### Efficiency and sustainability

Energy efficiency class	C
Annual energy consumption in kWh	589
Noise in dB(a) in the Cottons Normal dry standard programme with a full load	66
Duration in minutes in the standard programme	115
How it works	Vented
Load in kg	8.0

### Connection options

Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WiFi module (optional)	•
WiFiConn@ct	•

### Standards, test certificates and symbols

CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•

PDR 508 [EL]

Professional vented dryer, Little Giants, electrically heated  
with extremely short programme running times. Capacity 8.0 kg 8.0 kg in 84 min minutes.



EAN: 4002516527985 / Material number: 11945020 / Old Material Number: 52508353GB

UKCA

Complies with Machinery Directive 2006/42/EC

•  
•