

PDR 508 HP [EL]

Professional heat-pump dryer, Little Giants

With very low energy consumption and short running times. Load capacity 8.0 kg.



- Drum volume 130.00 l 130.00 l, load capacity 8.0 kg
- 50 % less energy consumption than vented dryers*
- Tested for intensive use – unparalleled Miele quality
- Language-neutral fascia panel with rotary control – M Select
- Precision drying of all fabrics – PerfectDry

* Heat pump dryers consume up to 50 % less energy than an electrically heated vented dryer.

A++

EAN: 4002516529323 / Material number: 11945090 / Old Material Number: 52508153IRL

Construction type and version

Construction type	Front-loader, stackable
Range	Performance
Front	Lotus white
Fascia color	Stainless steel
Load in kg	8.0
Drum volume in l	130.00
Drying system	Heat pump
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes

Application

Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for residential homes and apartments	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•

Performance data

Maximum evaporation capacity in l/hour	2.80
Specific energy consumption in kWh/kg	0.20
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.20
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.17
Programme duration in min.	79
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	79
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	67

Control system

Control system	M Select
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•

PDR 508 HP [EL]

Professional heat-pump dryer, Little Giants

With very low energy consumption and short running times. Load capacity 8.0 kg.



EAN: 4002516529323 / Material number: 11945090 / Old Material Number: 52508153IRL

Language can be selected easily at any time

Standard electrical connection	
Heating type	Heat pump
Electrical connection	220-240V~ 50HZ
Electric heater rating in kW	0.00
Total connected load in kW	1.44
Fuse rating in A	13
Dimensions and weight of dryer	
External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	777
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	70.0
Gross weight in kg	76
Maximum floor load in N/m ²	920
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.60
Features	
Intelligent drum reversal	•
Axial airflow	•
Fluff filter in the door	•
Low-maintenance heat exchanger filter system	•
PerfectDry	•
SoftLift drum ribs	•
Gentle tumble function	•
Condensed water drainage	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
Efficiency and sustainability	
Energy efficiency class	A++
Condensation efficiency class	A
Annual energy consumption in kWh	236
Noise in dB(a) in the Cottons Normal dry standard programme with a full load	67
Duration in minutes in the standard programme	103
How it works	Condenser
Load in kg	8.0
Contains fluorinated greenhouse gases	•
Hermetically sealed system	•
Coolant	R134a
Refrigerant quantity in kg	0.61
Refrigerant global warming potential in kg CO ₂ e	1430
Appliance global warming potential in kg CO ₂ e	872.00
Connection options	
Payment system (optional)	•
Optical interface for service access	•

PDR 508 HP [EL]
Professional heat-pump dryer, Little Giants
With very low energy consumption and short running times. Load capacity 8.0 kg.



EAN: 4002516529323 / Material number: 11945090 / Old Material Number: 52508153IRL

LAN/WiFi module (optional)	•
WiFiConn@ct	•
Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•