

Complete C2 Flex - SFAF5  
Cylinder vacuum cleaner  
with highly efficient motor for energy-efficient vacuuming.



- High suction power – 890 W
- Versatile applications – universal floorhead
- Easy vacuuming of larger areas with 10 m operating radius
- Convenient and versatile with three integrated accessories
- Long flexible crevice nozzle for cleaning narrow gaps

EAN: 4002516556282 / Material number: 12034860 / Old Material Number: 41FAF531GB

<b>Construction type</b>	
Cylinder vacuum cleaner with dustbag	•
Product brand	Complete C2
Motor type	PowerLine
Product type	SFAF5
Appliance Colour	Obsidian black
<b>User convenience</b>	
Electronic suction power control	6-stage rotary selector
Ergonomic carrying handle	•
Ergonomic handle	•
Silence system	•
Suction tube	Comfort telescopic tube
Park system for pauses during vacuuming	•
Park system	Both sides
<b>Efficiency and sustainability</b>	
Nominal power consumption in W	890
<b>Mobility</b>	
Castors with steel shaft, gentle on floors	•
3-point manoeuvrability	•
Operating radius in m	10
Cable length in m	6.5
<b>Filter system</b>	
Vacuum cleaner bag type	HyClean GN
Dustbag volume in l	4.5
Dustbag change indicator	•
Exhaust filter	AirClean filter
Motor protection filter	•
<b>Safety</b>	
Locking system for floorhead and handle	•
Automatic dustbag positioning	•
All-round furniture protection strip	•
<b>Technical data</b>	
Max. power	890
Volume in dB	80.0
Diameter in mm	487
Height in mm	227
Weight in kg	7.0
<b>Accessories supplied</b>	
Three-piece accessory set	Integrated
Upholstery nozzle	•
Extra long, flexible crevice nozzle SDF 20	•
Dusting brush with synthetic bristles	•
Floorhead SBD 355-3	•
Filter	AirClean filter
Cleaning tool	No