

KD 4172 E Active
 Freestanding fridge-freezer
 with DailyFresh, DuplexCool & ComfortFrost for an affordable entry-level price.



- Spacious drawer with moisture control – DailyFresh
- Two separate air circuits for optimum cooling – DuplexCool
- Less frequent defrosting thanks to ComfortFrost
- More space for particularly large frozen food – XXL box
- Handle-less design thanks to an integrated handle design



EAN: 4002516572398 / Material number: 12057230 / Old Material Number: 38417254GB

Appliance category	
Fridge-freezer	•
Construction type	
Freestanding appliance	•
Door hinge	right
Convertible door hinging	•
Design	
Casing colour	White
Front colour	White
Refrigeration section lighting	LED
User convenience	
Freshness system	DailyFresh
ComfortFrost	•
VarioRoom	•
Concealed door opener	SideOpen
Control system	
Operating concept	EasyControl
Precise adjustment	Fridge temperature
Independent temperature regulation of fridge and freezer zones	No
SuperFreeze	•
No. of temperature zones	2
Fridge/Fridge section	
No. of shelves	4
Chrome-plated metal bottle rack	•
No. of crisper drawers	1
Number of inner door racks for tinned food	2
Door rack for bottles	1
Door shelves	3
Freezer/Freezer section	
Number of freezer drawers including XXL box	3 1
Efficiency and sustainability	
Energy efficiency class (A–G)	E
Annual energy consumption in kWh	233.00
Energy consumption in 24 h in kWh	0.63
Safety	
Acoustic door alarm	•
Technical data	
Appliance width in mm	600
Appliance height in mm	1860
Appliance depth in mm	650
Weight in kg	73.9
Climate class	SN-T
Refrigerator compartment in l	214
4* freezer compartment in l	94
Total usable capacity in l	308
Storage time in case of fault in h	17
Freezer capacity in kg/24 h	4.50
Acoustic airborne noise emission class (A–D)	C


KD 4172 E Active
Freestanding fridge-freezer
with DailyFresh, DuplexCool & ComfortFrost for an affordable entry-level price.




EAN: 4002516572398 / Material number: 12057230 / Old Material Number: 38417254GB

Sound emissions in dB(A) re 1 pW	39
Current consumption (mA)	900
Voltage in V	220-240
Fuse rating in A	13
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2.1
Replacing lamps	Service
Accessories included	
Egg tray	•
Ice cube tray	•


KD 4172 E Active
 Freestanding fridge-freezer
 with DailyFresh, DuplexCool & ComfortFrost for an affordable entry-level price.



KF4372CD, KD4172E Active, KD4072E Active, installation sketch (installation drawings)



KF4372CD, KF4392CD, KD4050E Active, KD4052E Active, KD4072E Active, KD4172E Active, top view (installation drawings)



KDN4071E, KDN4074E, KDN4174E, KD4050E, KD4052E, KD4072E, KD4172E, connection sketch (footnote*) (installation drawings)

*1. View from the front, 2. Mains connection cable, L 2400 mm