

## DGC 7865 HCX Pro

Handleless combination steam oven with mains water and drain connection for steam cooking, baking, roasting with wireless food probe + HydroClean.



- Large touch display with proximity sensor – M Touch + MotionReact
- Perfect results – DualSteam technology
- Crispy outside, succulent inside – combination cooking
- Miele@home – network-enabled WiFi appliance + Mix & Match
- Easy cleaning – HydroClean and stainless steel oven compartment

A+

EAN: 4002516626510 / Material number: 12101760 / Old Material Number: 23786579GB

| Construction type and design                                     |               |
|--|---------------|
| Steam combination oven   | •             |
| ArtLine  | •             |
| Handleless   | •             |
| Appliance Colour   | Graphite grey |
| Convenience features   |               |
| Rapid heat-up  | •             |
| Pre-heating  | •             |
| External steam generation  | •             |
| Oxygen sensor  | •             |
| Individual humidity settings in combination cooking              | •             |
| Menu cooking without transfer of taste                           | •             |
| Mix & Match  | •             |
| Food probe   | Without cable |
| Automatic programmes with ability to make individual adjustments | •             |
| Keeping warm   | •             |
| Crisp function   | •             |
| Operating modes  |               |
| Defrost  | •             |
| Automatic programmes   | •             |
| Country-specific automatic programmes                            | •             |
| Combination cooking  | •             |
| Combination cooking with Fan plus                                | •             |
| Combination cooking with Conventional heat                       | •             |
| Combination cooking with grill large                             | •             |
| Steam cooking  | •             |
| Sous-vide  | •             |
| Reheat   | •             |
| Roast with moisture  | •             |
| Grill operating modes  | •             |
| Grill  | •             |
| Economy grill  | •             |
| Fan plus   | •             |
| Intensive bake   | •             |
| Cake plus  | •             |
| Conventional heat  | •             |
| Top heat   | •             |
| Bottom heat  | •             |
| Fan grill  | •             |
| Eco hot air  | •             |
| Eco steam cooking  | •             |
| Plate warming  | •             |
| Special applications   | •             |
| User convenience   |               |
| Networking with Miele@home                                       | •             |
| Display  | M Touch       |
| MotionReact proximity sensor                                     | •             |
| MotionReact: light comes on when movement is detected            | •             |

## DGC 7865 HCX Pro

Handleless combination steam oven with mains water and drain connection for steam cooking, baking, roasting with wireless food probe + HydroClean.



EAN: 4002516626510 / Material number: 12101760 / Old Material Number: 23786579GB

|   |     |
|---|-----|
| MotionReact: display comes on when movement is detected               | •   |
| MotionReact: audible signal is acknowledged when movement is detected | •   |
| MotionReact: detection of cabinet fronts                              | •   |
| SoftOpen  | •   |
| Touch2Open  | •   |
| MultiLingua   | •   |
| MyMiele   | •   |
| Help function   | •   |
| Motorised lift-up control panel with SoftClose                        | •   |
| Quantity-independent cooking  | •   |
| Steam cooking on up to 4 levels at the same time                      | •   |
| Automatic menu cooking  | •   |
| Steam reduction before end of programme                               | •   |
| Polyphonic buzzers  | •   |
| Time of day display   | •   |
| Date display  | •   |
| Minute minder   | •   |
| Programmable start of cooking duration                                | •   |
| Programmable end of cooking duration                                  | •   |
| Programmable cooking duration   | •   |
| Actual temperature display  | •   |
| Target temperature display  | •   |
| Buzzer when desired temperature is reached                            | •   |
| Recommended temperature   | •   |
| User programmes   | •   |
| Individual settings   | •   |
| <b>Efficiency and sustainability</b>                                  |     |
| Energy efficiency class (A+++ - D)                                    | A+  |
| Power rating in off mode in W   | 0.5 |
| Power rating in standby mode in W                                     | 1.0 |
| Power rating in networked standby in W                                | 2.0 |
| Time until automatic switch to standby in min                         | 20  |
| Time until automatic switch to networked standby in min               | 20  |
| Time until automatic switch to off mode in min                        | 20  |
| <b>Cleaning and care</b>  |     |
| Stainless-steel oven compartment with linen structure                 | •   |
| Hinged grill element  | •   |
| External steam generator  | •   |
| HydroClean  | •   |
| Maintenance programmes  | •   |
| Soak programme  | •   |
| Rinse programme   | •   |
| Oven compartment drying programme                                     | •   |
| Quick-release side racks  | •   |
| Removable stainless-steel side racks                                  | •   |
| Automatic descaling   | •   |
| CleanGlass door   | •   |
| <b>Steam techn./water supply</b>                                      |     |
| DualSteam   | •   |

## DGC 7865 HCX Pro

Handleless combination steam oven with mains water and drain connection  
for steam cooking, baking, roasting with wireless food probe + HydroClean.

EAN: 4002516626510 / Material number: 12101760 / Old Material Number: 23786579GB

|   |                 |
|---|-----------------|
| Steam generator power in kW                         | 3.30            |
| DirectWater Plus                                    | •               |
| Drain filter  | •               |
| <b>Safety</b>                                       |                 |
| Appliance cooling system and touch-cool front       | •               |
| Safety switch-off                                   | •               |
| System lock   | •               |
| Vapour cooling system                               | •               |
| Sensor lock   | •               |
| <b>Technical data</b>                               |                 |
| Oven compartment volume in l                        | 67              |
| No. of shelf levels                                 | 4               |
| Numbered shelf levels                               | •               |
| Door hinge  | Bottom          |
| Oven light  | BrilliantLight  |
| Oven mode temperatures min. in °C                   | 30              |
| Oven mode temperatures max. in °C                   | 230             |
| Steam-cooking mode temperatures min. in °C          | 40              |
| Steam-cooking mode temperatures max. in °C          | 100             |
| Niche width min. in mm                              | 560             |
| Niche width max. in mm                              | 568             |
| Niche height min. in mm                             | 590             |
| Niche height max. in mm                             | 595             |
| Niche depth in mm                                   | 550             |
| Appliance dimensions (W x H x D) in mm              | 595 x 596 x 567 |
| Appliance width in mm                               | 595             |
| Appliance height in mm                              | 596             |
| Appliance depth in mm                               | 567             |
| Weight in kg  | 46.4            |
| Total rated load in kW                              | 3.45            |
| Voltage in V  | 230             |
| Frequency in Hz                                     | 50              |
| Fuse rating in A                                    | 16              |
| Number of phases                                    | 1               |
| Mains cable with plug                               | •               |
| Length of supply lead in m                          | 2               |
| Length of water inlet hose in m                     | 2.0             |
| Length of water drain hose in m                     | 3.0             |
| Replacing lamps                                     | Service         |
| <b>Accessories included</b>                         |                 |
| Universal tray with PerfectClean                    | 1               |
| Baking and roasting rack with PerfectClean          | 1               |
| FlexiClip runners with PerfectClean                 | 1               |
| Removable side runners (pair)                       | 1               |
| No. of perforated stainless-steel cooking container | 2               |
| No. of solid stainless-steel cooking containers     | 1               |
| HydroClean cleaning agent                           | 1               |
| Descaling tablets                                   | 2               |

## DGC 7865 HCX Pro

Handleless combination steam oven with mains water and drain connection for steam cooking, baking, roasting with wireless food probe + HydroClean.



EAN: 4002516626510 / Material number: 12101760 / Old Material Number: 23786579GB


### Available display languages

Available display languages via MultiLingua


bahasa malaysia, dansk,  
deutsch, english, español,  
français, hrvatski, italiano,  
magyar, nederlands,  
norsk, polski, portugês,  
русский, română,  
slovenčina, slovenščina,  
srpski, suomi, svenska,  
türkçe, українська, čeština,  
ελληνικά,

## DGC 7865 HCX Pro


Handleless combination steam oven with mains water and drain connection for steam cooking, baking, roasting with wireless food probe + HydroClean.




ESW7x20, DGC7x6xHCPro, DGC7x6xHCXPro installation drawings




ESW7x10, EVS7010, DGC7x6xHCPro, DGC7x6xHCXPro installation drawings




built-in DGC XXL, installation drawing




built-in DGC XXL build-under, installation drawing  
Worktop overhang ≤ 29 mm




screw joint DGC XXL, installation drawing



DGC7x4x swivel range of the aperture, installation drawings



side view DGC XXL, installation drawings



Seitenansicht DGC XXL, installation drawing, GB, AU  
22 mm glass, 23.3 mm stainless steel