

CM 5315 Active
Countertop coffee machine
with OneTouch for Two for the ultimate in coffee enjoyment.

- Two coffees at once at the touch of a button – OneTouch for Two
- Perfect results and intense coffee flavour – AromaticSystem
- Creamy milk froth for a wide range of coffee specialities
- Convenient cleaning and maintenance programmes
- Convenient when hosting lots of guests – coffee/tea pot function

EAN: 4002516602323 / Material number: 12140370 / Old Material Number: 29531510GB

Construction type and design	
Freestanding bean-to-cup coffee machine	•
Colour	Graphite grey
Convenience features	
AromaticSystem	•
OneTouch preparation	•
OneTouch for Two preparation	•
Aroma-friendly conical grinder	•
Selectable grinder setting	•
Additional coffee types in ground coffee form possible	•
Programmable amount of coffee	•
Programmable amount of water	•
Programmable water temperature	•
Amount of milk can be programmed	•
Programmable amount of milk froth	•
Pre-brewing programmable	•
User convenience	
Display	DirectSensor
Height adjustable central spout, range in cm	8.0
Height adjustable central spout, range in cm	13.5
MultiLingua	•
No. of bean types	1
No. of bean containers	1
Capacity of bean container A in g	200
Bean container capacity, total in g	200
Capacity of water container in l	1.3
Drip tray capacity	0.8
Easily accessible containers	•
Programmable standby time	•
Programmable settings	•
Beverages	
Selectable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Caffè latte, single	•
Caffè latte, double	•

CM 5315 Active
 Countertop coffee machine
 with OneTouch for Two for the ultimate in coffee enjoyment.

EAN: 4002516602323 / Material number: 12140370 / Old Material Number: 29531510GB

Coffee pot	•
Efficiency and sustainability	
Energy-saving eco-mode selectable	•
Cleaning convenience	
Manual descaling	•
Automatic rinsing of milk pipework with water from the water container	•
Convenient cleaning programmes	•
Automatic rinsing function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•
Programmable water hardness	•
Safety	
System lock	•
Technical data	
Appliance width in mm	0
Appliance height in mm	0
Appliance depth in mm	0
Total rated load in kW	1.45
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Length of supply lead in m	1.2
Accessories supplied	
Voucher for CJ 1 coffee pot	•
Descaling tablets	•
Cleaning tablets	•
Brief operating instructions on rear of unit	•
Available display languages	
Available display languages via MultiLingua	bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, português, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά, , , , ,