

KWT 4999 F
Freestanding wine unit
with SommelierSet, FlexiFrame and three separate temperature zones.



- A perfect ceremony of your favourite wines thanks to the SommelierSet
- Storage of all bottle sizes/shapes thanks to FlexiFrame
- Perfect drinking and storage temperatures thanks to separate temperature zones
- Perfect regulation of humidity with ActiveHumidity
- UV-resistant insulated glass
- Protect your favourite wines with an integrated door lock



EAN: 4002516612421 / Material number: 12156870 /
Old Material Number: 39499962EU1

| | |
|--|---------------------------|
| Appliance category | |
| Wine conditioning unit | • |
| Construction type | |
| Freestanding appliance | • |
| Door hinge | right |
| Convertible door hinging | • |
| Design | |
| Casing colour | BlackSteel |
| Front colour | Obsidian Black glass |
| Wine compartment lighting | continuously dimmable LED |
| User convenience | |
| Networking with Miele@home | • |
| SoftClose | • |
| Concealed door opener | SideOpen |
| Silence system | • |
| Number of shelves | 9 |
| Shelf material | Beechwood |
| Number of FlexiFrame racks | 9 |
| SelfClose FlexiFrame | • |
| SommelierSet | • |
| NoteBoard | Yes |
| Bottle presenter | • |
| Low-vibration storage | • |
| Control system | |
| Operating concept | FreshTouch |
| Independent temperature regulation of fridge and freezer zones | No |
| No. of temperature zones | 3 |
| Min. temperature setting range in °C | 5 |
| Max. temperature setting range in °C | 20 |
| Sabbath mode | • |
| Fridge/Fridge section | |
| Dry back wall | BlackSteel |
| ActiveHumidity | • |
| Efficiency and sustainability | |
| Energy efficiency class (A–G) | F |
| Annual energy consumption in kWh | 144.18 |
| Energy consumption in 24 h in kWh | 0.39 |
| Safety | |
| Lock function | • |
| Door lock | • |
| Acoustic door alarm | • |
| Acoustic temperature alarm | • |
| Optical door alarm | • |
| Optical temperature alarm | • |
| Technical data | |
| Appliance width in mm | 697 |


KWT 4999 F
 Freestanding wine unit
 with SommelierSet, FlexiFrame and three separate temperature zones.



EAN: 4002516612421 / Material number: 12156870 /
 Old Material Number: 39499962EU1


| | |
|--|-------------|
| Appliance height in mm | 2014 |
| Appliance depth in mm | 779 |
| Weight in kg | 158.0 |
| Climate class | SN-ST |
| Wine compartment in l | 562 |
| Total usable capacity in l | 562 |
| 0.75 l Bordeaux bottle capacity (no. of bottles) | 146 bottles |
| Acoustic airborne noise emission class (A–D) | B |
| Sound emissions in dB(A) re 1 pW | 35 |
| Current consumption (mA) | 1200 |
| Voltage in V | 220-240 |
| Fuse rating in A | 10 |
| Number of phases | 1 |
| Frequency in Hz | 50-60 |
| Length of supply lead in m | 2.0 |
| Accessories included | |
| Active AirClean filter | • |
| White chalk pen | • |

KWT 4999 F
 Freestanding wine unit
 with SommelierSet, FlexiFrame and three separate temperature zones.




KWT4999F obsw, KWT4995F obsw, Rioja, installation sketch (footnote*) (installation drawings)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KWT4999F obsw, KWT4995F obsw, Rioja, top view (footnote*) (installation drawings)

*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KWT4999F obsw, KWT4995F obsw, Rioja, installation (footnote*) (installation drawings)

*1. View from the front, 2. Mains connection cable, L = 2200 mm