

## KWT 4584 E

Freestanding wine storage unit  
with a temperature zone, ActiveHumidity and door lock.



- Perfect regulation of humidity with ActiveHumidity
- Protect your favourite wines with an integrated door lock
- Clever networking opens up new possibilities – Miele@home
- Presented in perfect light – LED lighting



EAN: 4002516612438 / Material number: 12156930 /  
Old Material Number: 39458451EU1

<b>Appliance category</b>	
Wine conditioning unit	•
<b>Construction type</b>	
Freestanding appliance	•
Door hinge	right
Convertible door hinging	•
<b>Design</b>	
Casing colour	black
Front colour	Black
Wine compartment lighting	LED illumination
<b>User convenience</b>	
Networking with Miele@home	•
Active AirClean filter	•
ActiveHumidity	•
Concealed door opener	SideOpen
Silence system	•
Total number of shelves	6
Number of shelves	5
Shelf material	Metal
Low-vibration storage	•
<b>Control system</b>	
Operating concept	SensorTouch
Independent temperature regulation of fridge and freezer zones	No
No. of temperature zones	1
Min. temperature setting range in °C	5
Max. temperature setting range in °C	20
Sabbath mode	•
<b>Fridge/Fridge section</b>	
Dry back wall	grey
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	E
Annual energy consumption in kWh	95.36
Energy consumption in 24 h in kWh	0.26
<b>Safety</b>	
Lock function	•
Door lock	•
Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
<b>Technical data</b>	
Appliance width in mm	597
Appliance height in mm	1884
Appliance depth in mm	764
Weight in kg	73.0
Climate class	SN-T
Wine compartment in l	433

KWT 4584 E

Freestanding wine storage unit

with a temperature zone, ActiveHumidity and door lock.




EAN: 4002516612438 / Material number: 12156930 /

Old Material Number: 39458451EU1

Total usable capacity in l	434
0.75 l Bordeaux bottle capacity (no. of bottles)	229 bottles
Acoustic airborne noise emission class (A–D)	C
Sound emissions in dB(A) re 1 pW	38
Current consumption (mA)	1500
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.0


## KWT 4584 E

Freestanding wine storage unit  
with a temperature zone, ActiveHumidity and door lock.




KWT4584E sw, Rioja, installation sketch (\*footnote)  
(installation drawings)

\*Dimension with wall spacers



KWT4584E sw, Rioja, top view (installation drawings)



KWT4584E sw, Rioja, installation (footnote\*) (installation  
drawings)

\*1. View from the front, 2. Mains connection cable, L =  
2200 mm