

## PDR 510 ROP [EL]

Professional vented dryer, electric heating

with M Select ROP residual moisture control for perfect drying results.



- Drum volume 180.00 l 180.00 l, load size 18 (8.0) lb (kg) kg – 10.0 kg 10.0 kg
- Unique, gentle fabric care – honeycomb drum
- Connected for the future using LAN and WiFi
- Tested for intensive use – unparalleled Miele quality
- Precision drying of all fabrics – PerfectDry

EAN: 4002516657170 / Material number: 12258050 / Old Material Number: 52510001GB

| Construction type and version                         |                               |
|---|-------------------------------|
| Construction type                                     | Front loader                  |
| Range   | Performance                   |
| Front   | Iron grey                     |
| Fascia color  | Stainless steel               |
| Load in kg  | 10.0                          |
| Load size with a load ratio of 1:22.5                 | 18 (8.0) lb (kg)              |
| Load size with a load ratio of 1:18                   | 10.0                          |
| Load ratio  | 1:18                          |
| Drum volume in l                                      | 180.00                        |
| Drying system   | Exhaust air                   |
| Door opening [Ø] in mm                                | 440                           |
| Door opening angle in degrees                         | 180                           |
| Door hinge  | left                          |
| Stainless steel honeycomb drum                        | Yes                           |
| Application   |                               |
| Suitable for the hotel and catering industry          | •                             |
| Suitable for retirement and care homes                | •                             |
| Suitable for launderettes                             | •                             |
| Suitable for residential homes and apartments         | •                             |
| Suitable for commercial laundries                     | •                             |
| Suitable for small businesses                         | •                             |
| Suitable for universities, nurseries, and schools     | •                             |
| Suitable for camp sites                               | •                             |
| Suitable for sports clubs                             | •                             |
| Suitable for beauty salons, spas, and fitness centres | •                             |
| Performance data                                      |                               |
| Maximum evaporation capacity in l/hour                | 7.40                          |
| Specific energy consumption in kWh/kg                 | 0.51                          |
| Programme duration in min.                            | 36                            |
| Control system  |                               |
| Control system  | M Select Benchmark            |
| Programmability                                       | Setting of defined parameters |
| User interface  | Residual moisture controlled  |
| Max. delay start in h                                 | 24                            |
| Time left display                                     | •                             |
| Control panel with easy-to-understand symbols         | •                             |
| Standard electrical connection                        |                               |
| Heating type  | Electric                      |
| Electrical connection                                 | 3N AC 400V 50/60HZ            |
| Electric heater rating in kW                          | 7.94                          |
| Total connected load in kW                            | 8.20                          |
| Fuse rating in A                                      | 16                            |
| Dimensions and weight                                 |                               |
| External dimensions, height in mm                     | 1020                          |
| External dimensions, width in mm                      | 700                           |
| External dimensions, depth in mm                      | 763                           |
| External dimensions, gross height in mm               | 1215                          |

## PDR 510 ROP [EL]

Professional vented dryer, electric heating

with M Select ROP residual moisture control for perfect drying results.



EAN: 4002516657170 / Material number: 12258050 / Old Material Number: 52510001GB

|   |                    |
|---|--------------------|
| External dimensions, gross width in mm          | 760                |
| External dimensions, gross depth in mm          | 820                |
| Net weight in kg                                | 72.0               |
| Gross weight in kg                              | 80                 |
| Maximum floor load in N/m <sup>2</sup>          | 853                |
| <b>Emissions data</b>                           |                    |
| Emission sound pressure level in the workplace  | 50 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h          | 3.90               |
| <b>Features</b>                                 |                    |
| Intelligent drum reversal                       | •                  |
| Axial airflow                                   | •                  |
| Large-surface filter                            | •                  |
| PerfectDry                                      | •                  |
| SoftLift drum ribs                              | •                  |
| Low temperature function                        | •                  |
| Communication slot                              | •                  |
| Drum lighting                                   | •                  |
| Machine-independent accessories                 | •                  |
| <b>Connection options</b>                       |                    |
| Payment system (optional)                       | •                  |
| Optical interface for service access            | •                  |
| Peak load cut-out/energy management (optional)  | •                  |
| WiFi tumble dryer                               | •                  |
| Connector Box                                   | •                  |
| LAN module (optional)                           | •                  |
| <b>Standards, test certificates and symbols</b> |                    |
| VDE   | •                  |
| VDE-EMC   | •                  |
| Splash-proof safety rating IPX4                 | •                  |
| WEEE  | •                  |
| UKCA  | •                  |
| Complies with Machinery Directive 2006/42/EC    | •                  |