

## PDR 910 [EL]

Professional vented dryer, electric heating  
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 180.00 l 180.00 l, load size 18 (8.0) lb (kg) kg – 10.0 kg 10.0 kg
- Unique, gentle fabric care – honeycomb drum
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi
- Tested for intensive use – unparalleled Miele quality

EAN: 4002516657910 / Material number: 12258500 / Old Material Number: 52910004GB

Construction type and version	
Construction type	Front loader
Range	Performance Plus
Front	Stainless steel
Fascia color	Stainless steel
Load in kg	10.0
Load size with a load ratio of 1:22.5	18 (8.0) lb (kg)
Load size with a load ratio of 1:18	10.0
Load ratio	1:18
Drum volume in l	180.00
Drying system	Exhaust air
Door opening [Ø] in mm	440
Door opening angle in degrees	180
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for laundrettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour	7.40
Specific energy consumption in kWh/kg	0.51
Programme duration in min.	63
Control system	
Control system	M Touch Pro
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•

## PDR 910 [EL]

Professional vented dryer, electric heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516657910 / Material number: 12258500 / Old Material Number: 52910004GB

Standard electrical connection	
Heating type	Electric
Electrical connection	1N AC 230V 50/60HZ
Electric heater rating in kW	5.22
Total connected load in kW	5.50
Fuse rating in A	25
Dimensions and weight	
External dimensions, height in mm	1020
External dimensions, width in mm	700
External dimensions, depth in mm	763
External dimensions, gross height in mm	1215
External dimensions, gross width in mm	760
External dimensions, gross depth in mm	820
Net weight in kg	72.0
Gross weight in kg	80
Maximum floor load in N/m <sup>2</sup>	853
Emissions data	
Emission sound pressure level in the workplace	50 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.90
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drum lighting	•
Programme selection via colour frame	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Respirator masks [number]	4
Overalls [number]	1
Over jackets [number]	2
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Down duvets [number]	1
Down pillows [number]	2
Cloths, 22 g [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Summer horse blankets [number]	2
Standards, test certificates and symbols	
VDE	•

PDR 910 [EL]

Professional vented dryer, electric heating  
with programmable M Touch Pro controls for the maximum in flexibility.