

## PDR 516 SL ROP [EL IGS]

Vented dryer, iron grey sides, electric

In SlimLine design, with residual moisture controls for perfect drying results.



- Very easy installation – only 711 mm wide
- Easy to move – direct access underneath
- Shortest cycles thanks to diagonal air flow
- Precision drying of all fabrics – PerfectDry

EAN: 4002516659594 / Material number: 12262520 / Old Material Number: 52516001GB

<b>Construction type and version</b>	
Construction type	SlimLine
Range	Professional
Front	Iron grey
Fascia color	Stainless steel
Load in kg	16.0
Load size with a load ratio of 1:25	12.0
Load size with a load ratio of 1:18	16.0
Load ratio	1:18
Drum volume in l	300.00
Drying system	Exhaust air
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Stainless steel drum	•
Stainless steel honeycomb drum	No
<b>Application</b>	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for commercial laundries	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
<b>Performance data</b>	
Maximum evaporation capacity in l/hour	12.50
Specific energy consumption in kWh/kg	0.55
Programme duration in min.	31
<b>Control system</b>	
Control system	M Select Benchmark
Programmability	Setting of defined parameters
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	3N AC 400V 50/60HZ
Electric heater rating in kW	13.50
Total connected load in kW	14.10
Fuse rating in A	25
<b>Dimensions and weight of dryer</b>	
External dimensions, height in mm	1800
External dimensions, width in mm	711
External dimensions, depth in mm	1089
External dimensions, gross height in mm	1810

## PDR 516 SL ROP [EL IGS]

Vented dryer, iron grey sides, electric

In SlimLine design, with residual moisture controls for perfect drying results.



EAN: 4002516659594 / Material number: 12262520 / Old Material Number: 52516001GB

External dimensions, gross width in mm	800
External dimensions, gross depth in mm	1180
Net weight in kg	145.7
Gross weight in kg	159
Maximum floor load in N/m <sup>2</sup>	1664
<b>Emissions data</b>	
Emission sound pressure level in the workplace	55 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.70
<b>Features</b>	
Intelligent drum reversal	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Retractable plinth	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•