

PDR 516 SL TOP [G IGS]

Vented dryer, iron grey sides, gas

in SlimLine design, with easy-to-use time control.



- Very easy installation – only 711 mm wide
- Easy to move – direct access underneath
- Shortest cycles thanks to diagonal air flow
- Simple operation – easy to clean large fluff filter

EAN: 4002516659792 / Material number: 12263090 / Old Material Number: 52516024GB

| Construction type and version | |
|---|-------------------------------|
| Construction type | SlimLine |
| Range | Professional |
| Front | Iron grey |
| Fascia color | Stainless steel |
| Load in kg | 16.0 |
| Load size with a load ratio of 1:25 | 12.0 |
| Load size with a load ratio of 1:18 | 16.0 |
| Load ratio | 1:18 |
| Drum volume in l | 300.00 |
| Drying system | Exhaust air |
| Door opening [Ø] in mm | 520 |
| Door opening angle in degrees | 180 |
| Door hinge | left |
| Stainless steel drum | • |
| Stainless steel honeycomb drum | No |
| Application | |
| Suitable for the hotel and catering industry | • |
| Suitable for retirement and care homes | • |
| Suitable for facility management | • |
| Suitable for laundrettes | • |
| Suitable for dry cleaners | • |
| Suitable for commercial laundries | • |
| Suitable for universities, nurseries, and schools | • |
| Suitable for hospitals | • |
| Suitable for sports clubs | • |
| Suitable for beauty salons, spas, and fitness centres | • |
| Performance data | |
| Maximum evaporation capacity in l/hour | 14.50 |
| Specific energy consumption in kWh/kg | 0.65 |
| Programme duration in min. | 27 |
| Control system | |
| Control system | M Select Benchmark |
| Programmability | Setting of defined parameters |
| User interface | time-controlled |
| Max. delay start in h | 24 |
| Time left display | • |
| Programme sequence indicator | • |
| Control panel with easy-to-understand symbols | • |
| Standard electrical connection | |
| Heating type | Gas |
| Electrical connection | 1N AC 230V 50/60HZ |
| Gas heater rating in kW | 18.00 |
| Total connected load in kW | 0.60 |
| Fuse rating in A | 10 |
| Dimensions and weight of dryer | |
| External dimensions, height in mm | 1800 |
| External dimensions, width in mm | 711 |
| External dimensions, depth in mm | 1089 |

PDR 516 SL TOP [G IGS]

Vented dryer, iron grey sides, gas

in SlimLine design, with easy-to-use time control.



EAN: 4002516659792 / Material number: 12263090 / Old Material Number: 52516024GB

| | |
|---|--------------------|
| External dimensions, gross height in mm | 1810 |
| External dimensions, gross width in mm | 800 |
| External dimensions, gross depth in mm | 1180 |
| Net weight in kg | 149.7 |
| Gross weight in kg | 163 |
| Maximum floor load in N/m ² | 1704 |
| Emissions data | |
| Emission sound pressure level in the workplace | 56 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h | 1.70 |
| Features | |
| Intelligent drum reversal | • |
| Large-surface fluff filter | • |
| SoftLift drum ribs | • |
| Retractable plinth | • |
| Machine-independent accessories | • |
| Connection options | |
| Payment system (optional) | • |
| Optical interface for service access | • |
| Peak load cut-out/energy management (optional) | • |
| WiFi tumble dryer | • |
| Connector Box | • |
| LAN module (optional) | • |
| Standards, test certificates and symbols | |
| CE | • |
| VDE | • |
| VDE-EMC | • |
| Splash-proof safety rating IPX4 | • |
| DVGW gas | • |
| WEEE | • |
| UKCA | • |
| Complies with Machinery Directive 2006/42/EC | • |