

## PDR 516 SL TOP [G GS]

Vented dryer, galvanised sides, gas heated  
in SlimLine design, with easy-to-use time control.



- Drum volume 300.00 l, load size 12.0 kg – 16.0 kg 16.0 kg
- Very easy installation – only 711 mm wide
- Easy to move – direct access underneath
- Shortest cycles thanks to diagonal air flow
- Simple operation – easy to clean large fluff filter

EAN: 4002516659808 / Material number: 12263140 /  
Old Material Number: 52516025GB

### Construction type and version

|                                     |                 |
|-------------------------------------|-----------------|
| Construction type                   | SlimLine        |
| Range                               | Performance     |
| Front                               | Iron grey       |
| Fascia color                        | Stainless steel |
| Load size with a load ratio of 1:25 | 12.0            |
| Load size with a load ratio of 1:18 | 16.0            |
| Drum volume in l                    | 300.00          |
| Drying system                       | Exhaust air     |
| Door opening [Ø] in mm              | 520             |
| Door opening angle in degrees       | 180             |
| Door hinge                          | left            |
| Stainless steel drum                | •               |
| Stainless steel honeycomb drum      | No              |

### Application

|   |   |
|---|---|
| Suitable for the hotel and catering industry          | • |
| Suitable for retirement and care homes                | • |
| Suitable for facility management                      | • |
| Suitable for laundrettes                              | • |
| Suitable for dry cleaners                             | • |
| Suitable for commercial laundries                     | • |
| Suitable for universities, nurseries, and schools     | • |
| Suitable for hospitals                                | • |
| Suitable for sports clubs                             | • |
| Suitable for beauty salons, spas, and fitness centres | • |

### Performance data

|  |       |
|--|-------|
| Maximum evaporation capacity in l/hour | 14.50 |
| Specific energy consumption in kWh/kg  | 0.65  |
| Programme duration in min.             | 27    |

### Control system

|   |                               |
|---|-------------------------------|
| Control system                                | M Select Benchmark            |
| Programmability                               | Setting of defined parameters |
| User interface                                | time-controlled               |
| Max. delay start in h                         | 24                            |
| Time left display                             | •                             |
| Programme sequence indicator                  | •                             |
| Control panel with easy-to-understand symbols | •                             |

### Standard electrical connection

|                            |                    |
|----------------------------|--------------------|
| Heating type               | Gas                |
| Electrical connection      | 1N AC 230V 50/60HZ |
| Gas heater rating in kW    | 18.00              |
| Total connected load in kW | 0.60               |
| Fuse rating in A           | 10                 |

### Dimensions and weight of dryer

|                                   |      |
|-----------------------------------|------|
| External dimensions, height in mm | 1800 |
| External dimensions, width in mm  | 711  |
| External dimensions, depth in mm  | 1089 |

## PDR 516 SL TOP [G GS]

Vented dryer, galvanised sides, gas heated  
in SlimLine design, with easy-to-use time control.



EAN: 4002516659808 / Material number: 12263140 /  
Old Material Number: 52516025GB

|   |       |
|---|-------|
| External dimensions, gross height in mm | 1810  |
| External dimensions, gross width in mm  | 800   |
| External dimensions, gross depth in mm  | 1180  |
| Net weight in kg                        | 149.7 |
| Gross weight in kg                      | 163   |
| Maximum floor load in N                 | 1704  |

### Emissions data

|  |                    |
|--|--------------------|
| Emission sound pressure level in the workplace | 56 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h         | 1.70               |

### Features

|                                 |   |
|---------------------------------|---|
| Intelligent drum reversal       | • |
| Large-surface fluff filter      | • |
| SoftLift drum ribs              | • |
| Retractable plinth              | • |
| Machine-independent accessories | • |

### Efficiency and sustainability

|                     |    |
|---------------------|----|
| Recycling rate in % | 93 |
|---------------------|----|

### Connection options

|  |   |
|--|---|
| Payment system (optional)                            | • |
| Optical interface for service access                 | • |
| Peak-load negotiation / energy management (optional) | • |
| WiFi   | • |
| Connector Box  | • |
| LAN module (optional)                                | • |

### Standards, test certificates and symbols

|  |   |
|--|---|
| CE   | • |
| VDE  | • |
| VDE-EMC                                      | • |
| Splash-proof safety rating IPX4              | • |
| DVGW gas                                     | • |
| WEEE   | • |
| UKCA   | • |
| Complies with Machinery Directive 2006/42/EC | • |