

## PDR 511 SL COP HP [EL IGS]

Heat-pump dryers

SlimLine, with time control, for connection to a payment system, 230 V.



- 60 % lower energy consumption than vented dryer\*
- Very easy installation – only 711 mm wide
- Easy to move – direct access underneath
- Shortest cycles thanks to diagonal air flow

\* Heat pump dryers consume up to 60 % less energy than an electrically heated vented dryer.

EAN: 4002516681274 / Material number: 12295730 / Old Material Number: 52511012GB

Construction type and version	
Construction type	SlimLine
Range	Professional
Front	Iron grey
Fascia color	Stainless steel
Load in kg	11.0
Load size with a load ratio of 1:25	8.0
Load size with a load ratio of 1:18	11.0
Load ratio	1:18
Drum volume in l	200.00
Drying system	Heat pump
Door opening [Ø] in mm	520
Door opening angle in degrees	180
Door hinge	left
Stainless steel drum	•
Stainless steel honeycomb drum	No
Application	
Suitable for launderettes	•
Performance data	
Maximum evaporation capacity in l/hour	4.50
Specific energy consumption in kWh/kg	0.22
Programme duration in min.	59
Control system	
Control system	M Select Benchmark
Programmability	Setting of defined parameters
User interface	time-controlled
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Standard electrical connection	
Heating type	Heat pump with CleanStream
Electrical connection	1N AC 230V 50HZ
Heater rating, heat pump in kW	6.40
Total connected load in kW	3.00
Fuse rating in A	16
Dimensions and weight of dryer	
External dimensions, height in mm	1800
External dimensions, width in mm	711
External dimensions, depth in mm	1075
External dimensions, gross height in mm	1810
External dimensions, gross width in mm	800
External dimensions, gross depth in mm	1180
Net weight in kg	192.7
Gross weight in kg	206
Maximum floor load in N/m <sup>2</sup>	2052
Emissions data	
Emission sound pressure level in the workplace	55 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	2.30

## PDR 511 SL COP HP [EL IGS]

Heat-pump dryers

SlimLine, with time control, for connection to a payment system, 230 V.



EAN: 4002516681274 / Material number: 12295730 / Old Material Number: 52511012GB

Features	
Intelligent drum reversal	•
Large-surface fluff filter	•
SoftLift drum ribs	•
Retractable plinth	•
Communication slot	•
Machine-independent accessories	•
Efficiency and sustainability	
Contains fluorinated greenhouse gases	•
Hermetically sealed system	•
Coolant	R450a
Refrigerant quantity in kg	1.35
Refrigerant global warming potential in kg CO <sub>2</sub> e	605
Appliance global warming potential in kg CO <sub>2</sub> e	877
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•