

G 7130 SC AutoDos
Freestanding dishwashers
with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Innovative design and maximum convenience – 3D MultiFlex Tray
- Communication with the machine could not be easier – Miele@home
- Everything completely dry – AutoOpen drying
- Fresh water dishwashers – from 6.0 l litres in the Automatic programme
- Very easy door opening and closing – ComfortClose



EAN: 4002516738336 / Material number: 12423690 /
Old Material Number: 21713016GB

Model	
Freestanding dishwasher	•
60 cm dishwasher	•
Design	
Control panel colour	Brilliant White
Control panel version	Straight fascia
Control type	Programme selector button
Display	1-line text display
Display colour	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	AutoClose
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	Display
Display language selection	•
Efficiency and sustainability	
Energy efficiency class (A–G)	B
Water consumption in the Automatic programme in l from	6.0
Water consumption of the ECO programme in litres per programme cycle	8.4
Electricity consumption in the ECO programme in kWh	0.64
Energy consumption of the ECO programme in kWh after 100 programme cycles	64
Consumption value in kWh in the ECO programme with hot water connection	0.40
Duration of ECO programme in minutes	199
Noise emission class	B
Noise emissions in dB(A)	43
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
BrilliantGlassCare	•
Wash programmes	
QuickPowerWash	•
ECO	•
Automatic	•
ComfortWash 45 °C	•
Intensive 75 °C	•
PowerWash	•

G 7130 SC AutoDos
 Freestanding dishwashers
 with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516738336 / Material number: 12423690 /
 Old Material Number: 21713016GB

ComfortWash+ 55 °C	•
Gentle	•
ExtraQuiet 39 dB(A)	•
Appliance care	•
Rinse out salt	•
Dishwashing options	
AutoDos	•
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
Basket design	
Cutlery loading	3D MultiFlex tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	ExtraComfort
Number of place settings	14
MultiClip	•
FlexCare Glass & Bottle	•
XL Assist	•
Safety	
Waterproof system	•
Filter indicator light	•
Safety lock	•
Technical data	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	845
Niche height maximal in mm	880
Niche depth in mm	600
Appliance width in mm	598
Appliance height in mm	845
Appliance depth in mm	600
Depth with door open in cm	119.5
Net weight in kg	56.0
Total rated load in kW	2.00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in cm	1.50
Length of water drain hose in cm	1.50
Length of supply lead in m	1.80
Available display languages	
Available display languages via MultiLingua	bahasa malaysia, deutsch, english (AU), english (GB), ? ? ? ? ? ? ? ? , ? ? ?


G 7130 SC AutoDos
Freestanding dishwashers
with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516738336 / Material number: 12423690 /
Old Material Number: 21713016GB

Accessories included	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

G 7130 SC AutoDos
Freestanding dishwashers
with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, free standing dishwasher, 60cm (installation drawing)