

G 7760 SCVi AutoDos  
Fully integrated dishwashers  
with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Innovative design and maximum convenience – 3D MultiFlex Tray
- Communication with the machine could not be easier – Miele@home
- Incredibly low sound emissions of just 41 dB(a) dB(A)
- Perfect illumination for easy loading – BrilliantLight
- All safely loaded where needed – Maxi comfort basket design



EAN: 4002516738466 / Material number: 12424000 / Old Material Number: 21776062GB

<b>Model</b>	
Fully integrated dishwasher	•
60 cm dishwasher	•
<b>Design</b>	
Control panel colour	Obsidian Black
Control panel version	Fully integrated fascia
Control type	Programme selector button
Display	1-line text display
Display colour	White
MultiLingua	•
<b>Convenience</b>	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	ComfortClose
BrilliantLight	•
Time left display	•
Delay start up to 24 hours	•
In-operation indicator light	optical and acoustic
Display language selection	•
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	A
Water consumption in the Automatic programme in l from	6,0
Water consumption of the ECO programme in litres per programme cycle	8,4
Electricity consumption in the ECO programme in kWh	0,54
Energy consumption of the ECO programme in kWh after 100 programme cycles	54
Consumption value in kWh in the ECO programme with hot water connection	0,29
Duration of ECO programme in minutes	230
Noise emission class	B
Noise emissions in dB(A)	41
FlexiTimer with EcoStart	•
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
<b>Quality of results</b>	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Recirculation Turbothermic drying	•
BrilliantGlassCare	•
<b>Wash programmes</b>	
ECO	•
Automatic	•
ComfortWash 45 °C	•
Intensive 75 °C	•
PowerWash	•
ComfortWash+ 55 °C	•

G 7760 SCVi AutoDos  
Fully integrated dishwashers  
with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516738466 / Material number: 12424000 / Old Material Number: 21776062GB

Gentle	•
QuickPowerWash	•
Hygiene	•
SolarSave	•
ExtraQuiet 37 dB(A)	•
Pasta/Paella	•
Tall items 65°C	•
Appliance care	•
Rinse out salt	•
<b>Dishwashing options</b>	
AutoDos	•
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
<b>Basket design</b>	
Cutlery loading	3D MultiFlex tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	MaxiComfort
Number of place settings	14
MultiClip	•
FlexCare Glass & Bottle	•
XL Assist	•
StrawClean	•
<b>Safety</b>	
Waterproof system	•
Filter indicator light	•
Safety lock	•
<b>Technical data</b>	
Niche width minimal in mm	600
Niche width max in mm	600
Niche height minimal in mm	805
Niche height maximal in mm	870
Niche depth in mm	550
Appliance width in mm	598
Appliance height in mm	805
Appliance depth in mm	550
Depth with door open in cm	116.5
Net weight in kg	48.0
Total rated load in kW	2.00
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Electrical frequency standard	50
Length of water inlet hose in cm	1.50
Length of water drain hose in cm	1.50
Length of supply lead in m	1.80
Min. front panel weight in kg	4.0
Max. front panel weight in kg	11.0

## G 7760 SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516738466 / Material number: 12424000 / Old Material Number: 21776062GB

[can be retrofitted by Service to min.]

7.0

[can be retrofitted by Service to max.]

14.0

Replacing lamps

Service

### Available display languages

Available display languages via MultiLingua

bahasa malaysia, deutsch,  
english (AU), english (GB),

### Accessories included

1 x PowerDisk

•

Voucher for 6 x PowerDisk

•

## G 7760 SCVi AutoDos

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, fully integrated dishwasher, 60cm (installation drawing)

- 1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm,
- 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),