


APLW 882

Retrofitting kit

potential-free contacts for activating external signal receivers for PLW 8636.



- 10 potential-free contacts (4 inputs and 6 outputs)
- For external pumps, valves, fans and ring line systems, for example
- Installed by Customer Service

EAN: 4002516744597 / Material number: 12426880 / Old Material Number: 69688200D

## Product category

Washer-disinfectors, laboratory

•

Cleaning machines for industrial parts cleaning

•

## Machine affiliation

PLW 8636 [IPC]

•

PLW 8636 [LAB / LAB MON]

•

## Product category

Conversion kit

•

Connection module with potential-free contacts

•

## Dimensions and weight

External dimensions, gross height in mm

74

External dimensions, gross width in mm

327

External dimensions, gross depth in mm

463

Net weight in kg

0.96

Gross weight in kg

1.33