

K 7767 D

Built-in refrigerator

DailyFresh, FlexiLight 2.0 and DynaCool for more convenience and flexibility.



- Spacious drawer with moisture control – DailyFresh
- Individually adjustable glass shelf lighting with FlexiLight 2.0
- Uniform temperature distribution inside the appliance – DynaCool
- Door shelf heights can be adjusted individually
- Dishwasher-proof door shelves – ComfortClean



EAN: 4002516747840 / Material number: 12444860 /
Old Material Number: 36776700GB

Appliance category	
Refrigerator	•
Construction type	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
Design	
Refrigeration section lighting	FlexiLight 2.0
Fan lighting	•
User convenience	
Networking with Miele@home	•
Freshness system	DailyFresh
Fine adjustment inner door	•
ComfortClean	•
DynaCool	•
ComfortSize	•
SoftClose	•
Control system	
Operating concept	FreshTouch
Fridge compartment can be switched off	No
Independent temperature regulation of fridge and freezer zones	No
SuperCool	•
No. of temperature zones	1
Sabbath mode	•
Party mode	•
Holiday mode	•
Fridge/Fridge section	
No. of shelves	7
including number of split shelves (FlexiBoard)	1
of which illuminated	4
Chrome-plated metal bottle rack	•
No. of crisper drawers	2
Number of inner door racks for tinned food	3
Door rack for bottles	2
Door shelves	5
Efficiency and sustainability	
Energy efficiency class (A–G)	D
Annual energy consumption in kWh	91.62
Energy consumption in 24 h in kWh	0.25
Safety	
Lock function	•
Acoustic door alarm	•
Optical door alarm	•
Technical data	
Niche width in mm min.	560
Niche width in mm max.	570

K 7767 D

Built-in refrigerator

DailyFresh, FlexiLight 2.0 and DynaCool for more convenience and flexibility.




EAN: 4002516747840 / Material number: 12444860 /
Old Material Number: 36776700GB

Niche height in mm min.	1772
Niche height in mm max.	1788
Niche depth in mm	550
Appliance width in mm	559
Appliance height in mm	1770
Appliance depth in mm	546
Weight in kg	58.6
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	26
Climate class	SN-T
Refrigerator compartment in l	311
Pantry compartment in l	311
Total usable capacity in l	311
Acoustic airborne noise emission class (A–D)	B
Sound emissions in dB(A) re 1 pW	33
Current consumption (mA)	1200
Voltage in V	220-240
Fuse rating in A	13
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.2
Replacing lamps	Service
Accessories included	
Egg tray	•

K 7767 D

Built-in refrigerator

DailyFresh, FlexiLight 2.0 and DynaCool for more convenience and flexibility.



K7733E, K7763E, K7732E, K7734F, K7764E, K7743E, K7744E, K7773D, K7774D (footnote*) (installation drawings)

*1. View from the front, 2. Mains connection cable, L = 2100 mm, 3. Ventilation cut-out min. 200 cm², 4. Ventilation, 5. No connections permitted in this area

K7733E, K7763E, K7732D, K7732E, K7734F, K7764E, K7743E, K7744E, K7773D, K7774D, built-in (footnote*) (drawings)

*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher.

K7733E, K7763E, K7732E, K7734F, K7764E, K7743E, K7744E, K7773D, K7774D, side view (installation drawings)