

G 7191 SCVi AD 125 Ed.

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



- Innovative design and maximum convenience – 3D MultiFlex Tray
- Communication with the machine could not be easier – Miele@home
- Everything completely dry – AutoOpen drying
- Fresh water dishwashers – from ?? litres in the Automatic programme
- Very easy door opening and closing – ComfortClose



EAN: 4002516763116 / Material number: 12469660 / Old Material Number: 21719162GB

| | |
|---|---------------------------|
| Anniversary promotion | |
| Anniversary models 125 | • |
| Model | |
| Fully integrated dishwasher | • |
| 60 cm dishwasher | • |
| Design | |
| Control panel colour | Stainless Steel. |
| Control panel version | Fully integrated fascia |
| Control type | Programme selector button |
| Display | 1-line text display |
| Display colour | White |
| MultiLingua | • |
| Convenience | |
| Networking with Miele@home | • |
| Automatic dispensing with PowerDisk | • |
| Door closing aid | ComfortClose |
| Time left display | • |
| Delay start up to 24 hours | • |
| In-operation indicator light | optical and acoustic |
| Display language selection | • |
| Efficiency and sustainability | |
| Energy efficiency class (A–G) | B |
| Water consumption in the Automatic programme in l from | 6.0 |
| Water consumption of the ECO programme in litres per programme cycle | 8.4 |
| Electricity consumption in the ECO programme in kWh | 0.64 |
| Energy consumption of the ECO programme in kWh after 100 programme cycles | 64 |
| Consumption value in kWh in the ECO programme with hot water connection | 0.40 |
| Duration of ECO programme in minutes | 199 |
| Noise emission class | B |
| Noise emissions in dB(A) | 43 |
| EcoFeedback | • |
| EcoPower Technology | • |
| Proven hygiene | • |
| Hot water connection | • |
| Half load | • |
| Quality of results | |
| Fresh water dishwasher | • |
| AutoOpen drying | • |
| SensorDry | • |
| Recirculation Turbothermic drying | • |
| BrilliantGlassCare | • |
| Wash programmes | |
| ECO | • |
| Automatic | • |
| ComfortWash 45 °C | • |
| Intensive 75 °C | • |
| PowerWash | • |
| Gentle | • |

G 7191 SCVi AD 125 Ed.

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516763116 / Material number: 12469660 / Old Material Number: 21719162GB

| | |
|--|--|
| QuickPowerWash | • |
| ExtraQuiet 40 dB(A) | • |
| Appliance care | • |
| Dishwashing options | |
| AutoDos | • |
| IntenseZone | • |
| Express | • |
| Extra Clean | • |
| Extra dry | • |
| Basket design | |
| Cutlery loading | 3D MultiFlex tray |
| FlexCare glass holder | 2 |
| FlexCare cup rack | 1 |
| Basket design | ExtraComfort |
| Number of place settings | 14 |
| MultiClip | • |
| Safety | |
| Waterproof system | • |
| Filter indicator light | • |
| Safety lock | • |
| Technical data | |
| Niche width minimal in mm | 600 |
| Niche width max in mm | 600 |
| Niche height minimal in mm | 805 |
| Niche height maximal in mm | 870 |
| Niche depth in mm | 550 |
| Appliance width in mm | 598 |
| Appliance height in mm | 805 |
| Appliance depth in mm | 550 |
| Depth with door open in cm | 116.5 |
| Net weight in kg | 47.0 |
| Total rated load in kW | 2.00 |
| Voltage in V | 230 |
| Fuse rating in A | 10 |
| Number of phases | 1 |
| Electrical frequency standard | 50 |
| Length of water inlet hose in cm | 1.50 |
| Length of water drain hose in cm | 1.50 |
| Length of supply lead in m | 1.80 |
| Min. front panel weight in kg | 4.0 |
| Max. front panel weight in kg | 11.0 |
| [can be retrofitted by Service to min.] | 7.0 |
| [can be retrofitted by Service to max.] | 14.0 |
| Available display languages | |
| Available display languages via MultiLingua | deutsch, english (AU), english (GB), , |
| Accessories included | |
| 1 x PowerDisk | • |
| Voucher for 6 x PowerDisk | • |
| Voucher for a box with rinse aid, dishwasher salt, DishClean | • |

G 7191 SCVi AD 125 Ed.

Fully integrated dishwashers

with automatic dispensing thanks to AutoDos with integrated PowerDisk.



G7000, fully integrated dishwasher, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm,
3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),