

## PWM 1108 SmartBiz [EL DP]

Washing machine, electrically heated

commercial quality with a cycle time of 79 min min., easy installation.



- Drum volume 64 l, load capacity 8.0 kg
- High-quality stainless steel control panel, Miele honeycomb drum
- Supplied ready for connection incl. mains plug
- Professional programme running time of just 79 min with a 8.0 kg load size
- Space-saving installation as washer-dryer stack



EAN: 4002516798910 / Material number: 12506880 / Old Material Number: 51110801GB

### Construction type and version

Construction type	Front-loader, stackable
Range	SmartBiz
Front	Lotus white
Load in kg	8.0
Drum volume in l	64
Door opening [Ø] in mm	300
Door opening angle in degrees	167
Door hinge	right
Maintenance-free synchronous motor	•
Stainless steel honeycomb drum	•

### Application

Suitable for the hotel and catering industry	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•

### Performance data

Specific water consumption for cold water connection in l / kg	6.50
Specific energy consumption for cold water connection in kWh/kg	0.16
Water consumption with cold water connection in l	52.0
Energy consumption with cold water connection in kW	1.30
Programme duration in minutes with cold water connection	79
Residual moisture with cold rinse in %	49
Spin speed in rpm	1400
g factor	535
Tested operating hours	15000

### Control system

Control system	DirectSensor 7-segment
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Fascia panel with plain text	•

### Dispensing

Detergent drawer	3 compartments
------------------	----------------

### Standard electrical connection

Heating type	Electric
Electrical connection	220-240V~ 50HZ
Heater rating in kW	1.90-2.20
Total connected load in kW	2.10-2.40
Fuse rating in A	13

### Water connection/drainage

Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22

### Dimensions and weight

External dimensions, height in mm	850
External dimensions, width in mm	596

## PWM 1108 SmartBiz [EL DP]

Washing machine, electrically heated

commercial quality with a cycle time of 79 min min., easy installation.



EAN: 4002516798910 / Material number: 12506880 / Old Material Number: 51110801GB

External dimensions, depth in mm	636
External dimensions, gross height in mm	944
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	690
Net weight in kg	91.0
Gross weight in kg	95
Maximum floor load in N/m <sup>2</sup>	2820
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1.00
<b>Features</b>	
Hard-wearing stainless-steel flange	•
Special heater element	•
Automatic load control	•
Machine-independent accessories	•
<b>Efficiency and sustainability</b>	
Energy efficiency class (A–G)	A
Spin efficiency class (A–G)	B
Weighted energy consumption per 100 cycles in the “eco 40–60” program in kWh	43
Weighted water consumption per cycle in the “eco 40–60” program in l	48
Noise emission rating (spin cycle) (A–D)	A
Noise emission during spin cycle in dB(A) re 1 pW	69
Program runtime in the “eco 40–60” program in min	219
Recycling rate in %	95
<b>Connection options</b>	
Optical interface for service access	•
WiFiConn@ct	•
<b>Standards, test certificates and symbols</b>	
CE	•
VDE-EMC	•
VDE	•
Splash-proof safety rating IPX4	•
UKCA	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•