

KU 7175 D

Built-under refrigerator, 86–92 cm niche height
with two individually adjustable temperature zones for more flexibility.



- From 0 °C for chilled drinks to 14 °C for an ideal cellar climate
- Optimal, maintenance-free interior lighting with LED
- Uniform temperature distribution inside the appliance – DynaCool
- Cleaning the VeggieBox in the dishwasher – ComfortClean
- Food is chilled quickly thanks to Automatic SuperCool
- Soft closing of the door with SoftClose



EAN: 4002516779315 / Material number: 12519370 / Old Material Number: 36717510EU1

General information	
Model identifier	KU 7175 D
Manufacturer material number	12519370
EAN number	4002516779315
Marketing class	Platinum
Appliance category	
Refrigerator	•
Construction type	
Integrated appliance	•
Undercounter appliance	•
Door hinge	Pull-out front
Design	
Refrigeration section lighting	LED
User convenience	
Networking with Miele@home	•
ComfortClean	•
DynaCool	•
Holiday mode	•
SoftClose	•
Control system	
Operating concept	FreshTouch
SuperCool	•
No. of temperature zones	2
Sabbath mode	•
Fridge/Fridge section	
No. of shelves	2
Efficiency	
Energy efficiency class (A–G)	D
Annual energy consumption in kWh	81.58
Energy consumption in 24 h in kWh	0.22
Safety	
Lock function	•
Acoustic door alarm	•
Optical door alarm	•
Technical data	
Niche width in mm min.	600
Niche width in mm max.	600
Niche height in mm min.	860
Niche height in mm max.	920
Niche depth in mm	560
Appliance dimensions (W x H x D) in mm	597 x 859 x 556
Appliance width in mm	597
Appliance height in mm	859
Appliance depth in mm	556
Weight in kg	42.2
Max. door front weight – refrigerator, in kg	10
Climate range	SN-T
Refrigerator compartment in l	119

KU 7175 D

Built-under refrigerator, 86–92 cm niche height
with two individually adjustable temperature zones for more flexibility.




EAN: 4002516779315 / Material number: 12519370 / Old Material Number: 36717510EU1


Of which pantry compartment in l	58.4
Total usable capacity in l	119
Acoustic airborne noise emission class (A–D)	B
Sound emissions in dB(A) re 1 pW	32
Current consumption (mA)	2000
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50-60
Length of supply lead in m	2.2
Replacing lamps	Service

KU 7175 D

Built-under refrigerator, 86–92 cm niche height
with two individually adjustable temperature zones for more flexibility.




KU7175D, Built-under, niche dimensions




KU7175D, Built-under, installation drawing (*footnote)

*1. View from the front, 2. Mains connection cable L = 2200 mm, 3. No connection in this area,



KU7175D, Built-under, side view



KU7175D, Built-under, side view