

FNUS 7040 D

Built-under freezer, 82–88 cm niche height

with NoFrost, SoftClose and SuperFreeze in a compact design. Requires kitchen fronts with a minimum height of 72 cm.



- No icing up of food and no need to defrost thanks to NoFrost
- Soft closing of the door with SoftClose
- Food is frozen quickly and gently – SuperFreeze
- Flexible increase in freezer volume – VarioRoom



EAN: 4002516779322 / Material number: 12519380 /
Old Material Number: 37704010EU1

General information	
Model identifier	FNUS 7040 D
Manufacturer material number	12519380
EAN number	4002516779322
Marketing class	Gold
Appliance category	
Freezer	•
Construction type	
Integrated appliance	•
Undercounter appliance	•
Door hinge	right
Convertible door hinging	•
Side-by-side enabled	•
Design	
Freezer compartment lighting	LED
User convenience	
Networking with Miele@home	•
NoFrost	•
VarioRoom	•
SoftClose	•
Smart Extras	
Push notifications	•
Cooling tips	•
Cooling modes	•
Smart Extras	
RemoteUpdate	•
Smart Home Integration	•
Control system	
Operating concept	FreshTouch
SuperFreeze	•
No. of temperature zones	1
Sabbath mode	•
Holiday mode	•
Freezer/Freezer section	
Number of freezer drawers	3
Efficiency	
Energy efficiency class (A–G)	D
Annual energy consumption in kWh	149.70
Energy consumption in 24 h in kWh	0.41
Safety	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer section	•
Technical data	
Niche width in mm min.	600

FNUS 7040 D

Built-under freezer, 82–88 cm niche height

with NoFrost, SoftClose and SuperFreeze in a compact design. Requires kitchen fronts with a minimum height of 72 cm.



EAN: 4002516779322 / Material number: 12519380 /

Old Material Number: 37704010EU1

Niche width in mm max.	600
Niche height in mm min.	820
Niche height in mm max.	880
Niche depth in mm	560
Appliance width in mm	597
Appliance height in mm	818
Appliance depth in mm	550
Weight in kg	36.0
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	10
Climate class	SN-T
4* freezer compartment in l	74
Total usable capacity in l	74
Storage time in case of fault in h	12
Freezer capacity in kg/24 h	8.20
Acoustic airborne noise emission class (A–D)	B
Sound emissions in dB(A) re 1 pW	32
Current consumption (mA)	2000
Voltage in V	220 - 240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50 - 60
Length of supply lead in m	2.2

Accessories included


Ice cube tray

•


FNUS 7040 D

Built-under freezer, 82–88 cm niche height

with NoFrost, SoftClose and SuperFreeze in a compact design. Requires kitchen fronts with a minimum height of 72 cm.




KU7016D, KU7015D, KU7035D, FNUS7040D, Built-under, niche dimensions



KU7016D, KU7015D, KU7035D, KU7135C, FNUS7140C, Built-under, installation drawing (*footnote)

*1. View from the front, 2. Mains connection cable, L = 2200 mm, 3. No connection in this area



KU7016D, KU7015D, KU7035D, FNUS7040D, Built-under, side view