

DAH 2960 Escala
Wall mounted cooker hood
with Con@ctivity and smart touch controls for convenience



- Lots of headroom – 898 mm 898 mm wide glass canopy
- Unique user convenience – Con@ctivity
- Efficient filtration- 10-ply stainless-steel grease filter
- Perfect match – glass panel and canopy in the same colour
- Suitable for every home – for extraction or recirculation



EAN: 4002516801504 / Material number: 12545640 / Old Material Number: 28H2960BGB

Construction type	
Wall mounted cooker hood	•
Construction type and design	
Colour	Obsidian black
Operating modes	
Type of air guide	Can be retrofitted
Active charcoal filter (order separately)	DKF 29 charcoal filter
Design	
Edge extraction	•
User convenience	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
ON/OFF switch	•
Booster levels	1
Easy-to-clean canopy interior – CleanCover	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	B
Annual energy consumption in kWh/year	72.3
Fluid dynamic efficiency class	B
Lighting efficiency class	A
Grease filtering efficiency class	D
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	2
Lighting	
LED	•
Number x W	1 x 3,2 W
Light intensity in Lx	300 lx
Colour temperature in K	3500 Kelvin
Fan	
Dual-action fan	•
AC motor	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	215
Air throughput in Level 2 (m ³ /h) according to EN 61591	315
Air throughput in Level 3 (m ³ /h) according to EN 61591	415
Air throughput in Booster level (m ³ /h) according to EN 61591	675
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	41.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	47.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	53.0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	65.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	27.0

DAH 2960 Escala
Wall mounted cooker hood
with Con@ctivity and smart touch controls for convenience



EAN: 4002516801504 / Material number: 12545640 / Old Material Number: 28H2960BGB

Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	33.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	39.0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	51.0
Recirculation	
Air throughput in Level 1 (m ³ /h) according to EN 61591	190
Air throughput in Level 2 (m ³ /h) according to EN 61591	280
Air throughput in Intensive level (m ³ /h) according to EN 61591	575
Air throughput in Level 3 (m ³ /h) according to EN 61591	380
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	47.0
Noise power level in Intensive level (dB(A) re 1 pW) according to EN 60704-3	71.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	54.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	60.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	33.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	40.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	46.0
Noise pressure level in Intensive level (dB(A) re 20 µPa) according to EN 60704-2-13	57.0
Safety	
Safety switch-off	•
Single-ply safety glass (ESG)	•
Technical data	
Overall hood height for extraction mode and external in mm	830-1210
Overall hood height for recirculation and external in mm	443
Overall height for vented and external in in. (mm)	830
Canopy width in mm	898
Overall height for extraction mode and external mode cooker hoods in mm	1210
Canopy height in mm	443
Overall height for recirculation in in. (mm)	443
Canopy depth in mm	388
Overall height for recirculation mode cooker hoods in mm	443
Minimum height above electric hobs in mm	450
Net weight in kg	18.0
Length of supply lead in m	1.3
Standard plug fitted	•
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Total rated load in kW	0.20
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50



DAH 2960 Escala
Wall mounted cooker hood
with Con@ctivity and smart touch controls for convenience



EAN: 4002516801504 / Material number: 12545640 / Old Material Number: 28H2960BGB

Installation notes	
Extraction ducting connection at top	•
Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Accessories included	
Non-return flap	•
Optional accessories	
Active charcoal filter	Nein

DAH 2960 Escala
Wall mounted cooker hood
with Con@ctivity and smart touch controls for convenience



DAH2960 Installation drawings

1) Break-through if the mains connection is not made with a mains plug, but with a fixed connection., 2) Exhaust air opening \varnothing 200 mm, so that the exhaust air line can be moved in the wall. Exhaust air connection \varnothing 150 mm to the top or alternatively to the rear., 3) Air outlet for recirculated air. The distance to the ceiling or furniture mounted above the unit should be at least 300 mm.