

WED385 WCS PWash&Steam&9kg

W1 front-loader washing machine:

A -20 %* | 9 kg | 1400 rpm | SteamCare | QuickPowerWash | Miele@home



- Tested for 20 years of perfect laundry care*
- Save even more energy with A -20 %**
- 50% less ironing plus maximum variety of applications –SteamCare
- Cleaning cannot be faster – QuickPowerWash
- Miele@home – clever networking opens up new possibilities***

* During the development phase of the W1 washing machine series, Miele tested models and core components in 5000 wash loads (= 5 wash loads per week for 50 weeks per year) in various programmes. More: miele.com/20years

** 20 % more economical than the threshold value (52) for energy efficiency class A.

*** Additional digital offer from Miele & Cie. KG. All smart applications are made possible with the Miele@home system. The range of functions can vary depending on the model and the country.



EAN: 4002516865759 / Material number: 12721260 / Old Material Number: 11ED3851GB

Construction type

Suitable for stacking	•
Side-by-side	•
Slot-in	•
Can be built-under	•
Door hinge	right

Model

Product brand	W1 Chrome Edition
Front-loader	•

Spinning

Max. spin speed	1400
Rinse hold	•
Without spin function	•

Design

Appliance colour	Lotus white
Control panel colour	Lotus white
Door design	Graphite grey PearlFinish
Rotary selector colour	Lotus White
Control panel version	Straight
Control type	Rotary control
Display	DirectSensor white, 7 segment

Cleaning performance

Innovative PowerWash technology	•
CapDosing portioned dispensing	•

Gentle laundry care

Honeycomb drum	•
Load in kg	9.0

User convenience

Networking with Miele@home	•
Delay start up to 24 hours	•
Time left display	•
AutoClean detergent drawer	•
AddLoad	•

Efficiency and sustainability

Energy efficiency class (A–G)	A
More economical than the threshold value (52) for energy efficiency class A	20%
Weighted energy consumption per 100 operating cycles for the wash cycle in kWh	40
Weighted water consumption per cycle in l	50
Spin efficiency class (A–G)	B
Acoustic airborne noise emission class (spin cycle; A–D)	A
Sound emissions during spin cycle in dB(A) re 1 pW	72
Duration of the "ECO 40–60" programme at nominal capacity	229
Power rating in off mode in W	0.30
Power rating in networked standby in W	0.60
Low temperature wash "Cold" and "20 °C"	•

WED385 WCS PWash&Steam&9kg

W1 front-loader washing machine:

A -20 %* | 9 kg | 1400 rpm | SteamCare | QuickPowerWash | Miele@home




EAN: 4002516865759 / Material number: 12721260 / Old Material Number: 11ED3851GB

Automatic load control	•
Flow meter	•
Foam sensing	•
ProfiEco motor	•
Wash programmes	
QuickPowerWash	•
Cottons (coloureds)	•
Minimum iron	•
Delicates	•
Shirts	•
Woollens (hand-washable)	•
Express 20	•
Dark garments / Denim	•
Freshen up (steam)	•
Drain / Spin	•
ECO 40-60	•
Washing extras	
Short	•
Pre-wash	•
Water plus	•
Additional rinse cycle	•
Pre-ironing with steam	•
Buzzer	•
Safety	
Water protection system	Watercontrol-System
Safety lock	•
PIN-Code	•
Optical interface	•
Technical data	
Dimensions in mm (width)	596
Dimensions in mm (height)	850
Dimensions in mm (depth)	636
Appliance depth in mm with opened door	1054
Appliance depth excluding door (for building-under) in mm	600
Weight in kg	80
Total rated load in kW	2.10-2.40
Voltage in V	220-240
Fuse rating in A	13
Frequency in Hz	50
Length of water inlet hose in m	1.60
Length of water drain hose in m	1.50
Length of supply lead in m	2


WED385 WCS PWash&Steam&9kg

W1 front-loader washing machine:


A -20 %* | 9 kg | 1400 rpm | SteamCare | QuickPowerWash | Miele@home




W1 installation drawing, slanted fascia or straight fascia, measures in mm



W1 drawing, slanted fascia or straight fascia, measures in mm



W1 drawing, slanted fascia or straight fascia, measures in mm



W1 drawing, slanted fascia or straight fascia, measures in mm