

PDR 508 ROP [EL]

Professional vented dryer, Little Giants, electrically heated
with extremely short programme running times. Performance 8.0 kg in 42 min.



- Drum volume 130.00 l, load capacity 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Language-neutral fascia panel with rotary control – M Select
- Precision drying of all fabrics – PerfectDry

EAN: 4002516870562 / Material number: 12752020 /
Old Material Number: 52508362IRL

Construction type and version

Construction type	Front-loader, stackable
Range	Performance
Front	Lotus white
Fascia color	Stainless steel
Load in kg	8.0
Drum volume in l	130.00
Drying system	Exhaust air
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes

Application

Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•

Performance data

Maximum evaporation capacity in l/hour	5 l
Specific energy consumption in kWh/kg	0.50
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.50
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.42
Programme duration in min.	52
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	52
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	47

Control system

Control system	M Select
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•

PDR 508 ROP [EL]

Professional vented dryer, Little Giants, electrically heated
with extremely short programme running times. Performance 8.0 kg in 42 min.



EAN: 4002516870562 / Material number: 12752020 /
Old Material Number: 52508362IRL

Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Language can be selected easily at any time	•
Standard electrical connection	
Heating type	Electric
Electrical connection	3N~ 400V 50/60HZ
Electric heater rating in kW	5.22
Total connected load in kW	5.47
Fuse rating in A	13
Possible voltage variant 1	
Electrical connection	230V~ 50/60HZ
Heater rating in kW	2.99
Total connected load in kW	3.24
Fuse rating in A	16
Possible voltage variant 2	
Electrical connection	3~ 230V 50/60HZ
Heater rating in kW	6.14
Total connected load in kW	6.40
Fuse rating in A	16
Dimensions and weight of dryer	
External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	717
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	49.0
Gross weight in kg	54
Maximum floor load in N	920
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	0.76
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
Efficiency and sustainability	
How it works	Vented
Recycling rate in %	95
Connection options	
Payment system (optional)	•

PDR 508 ROP [EL]

Professional vented dryer, Little Giants, electrically heated
with extremely short programme running times. Performance 8.0 kg in 42 min.



EAN: 4002516870562 / Material number: 12752020 /
Old Material Number: 52508362IRL

Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
WiFi	•
LAN module (optional)	•
WiFiConn@ct	•
Standards, test certificates and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•