

PDR 908 ROP [EL]

Professional vented dryer, Little Giants, electrically heated
with extremely short programme running times. Performance 8.0 kg in 42 min.



- Drum volume 130.00 l, load capacity 8.0 kg
- Tested for intensive use – unparalleled Miele quality
- Max. user convenience, full-touch colour display – M Touch Flex
- Precision drying of all fabrics – PerfectDry
- Future-proof networking via WiFi

EAN: 4002516870821 / Material number: 12752040 /
Old Material Number: 52908464IRL

Construction type and version

Construction type	Front-loader, stackable
Range	Performance Plus
Front	Stainless steel
Fascia color	Stainless steel
Load in kg	8.0
Drum volume in l	130.00
Drying system	Exhaust air
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes

Application

Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for laundrettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemicals industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks & holiday complexes	•

Performance data

Maximum evaporation capacity in l/hour	4 l
Specific energy consumption in kWh/kg	0.53
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.53
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.42
Programme duration in min.	54
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	54
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	45

Control system

Control system	M Touch Flex
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•

PDR 908 ROP [EL]

Professional vented dryer, Little Giants, electrically heated
with extremely short programme running times. Performance 8.0 kg in 42 min.



EAN: 4002516870821 / Material number: 12752040 /

Old Material Number: 52908464IRL

Language can be selected easily at any time

Standard electrical connection

Heating type	Electric
Electrical connection	230V~ 50/60HZ
Electric heater rating in kW	5.22
Total connected load in kW	5.47
Fuse rating in A	25

Dimensions and weight of dryer

External dimensions, height in mm	850
External dimensions, width in mm	605
External dimensions, depth in mm	717
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	51.5
Gross weight in kg	57
Maximum floor load in N	920

Emissions data

Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	0.76

Features

Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drum lighting	•
Machine-independent accessories	•

Efficiency and sustainability

How it works	Vented
Recycling rate in %	95

Connection options

Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
WiFi	•
LAN module (optional)	•
WiFiConn@ct	•

Standards, test certificates and symbols

CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
Complies with Machinery Directive 2006/42/EC	•