

PDR 307 ROP [EL]

Professional vented dryer, Little Giants, electrically heated
with a shortest cycle time of 77 min for a high throughput of laundry.



- Drum volume 130.00 l, load capacity 7.0 kg
- Tested for intensive use – unparalleled Miele quality
- Language-neutral fascia panel with rotary control – M Select
- Precision drying of all standard fabrics – PerfectDry

EAN: 4002516870852 / Material number: 12752470 /
Old Material Number: 52307362GB

Construction type and version

Construction type	Front-loader, stackable
Range	Evolution
Front	Lotus white
Fascia color	Stainless steel
Load in kg	7.0
Drum volume in l	130.00
Drying system	Exhaust air
Door opening [Ø] in mm	370
Door opening angle in degrees	167
Door hinge	left
Stainless steel honeycomb drum	Yes

Application

Suitable for the hotel and catering industry	•
Suitable for residential homes and apartments	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for domestic use	•
Suitable for amusement parks & holiday complexes	•
Suitable for state/community care facilities	•

Performance data

Maximum evaporation capacity in l/hour	3 l
Specific energy consumption in kWh/kg	0.49
Specific energy consumption for Cottons/Normal drying programme with residual moisture at 48 % in kW	0.49
Specific energy consumption for mixed fibre fabrics/Normal drying programme with residual moisture a	0.41
Programme duration in min.	77
Programme duration for Cottons/Normal drying programme with residual moisture at 48 % in minutes	77
Programme duration for mixed fibre fabrics/Normal drying programme with residual moisture at 40 % in	66

Control system

Control system	M Select
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Control panel with easy-to-understand symbols	•
Language can be selected easily at any time	•

Standard/target grp programmes

Basic programmes	•
------------------	---

Standard electrical connection

Heating type	Electric
--------------	----------

PDR 307 ROP [EL]

Professional vented dryer, Little Giants, electrically heated
with a shortest cycle time of 77 min for a high throughput of laundry.



EAN: 4002516870852 / Material number: 12752470 /
Old Material Number: 52307362GB

Electrical connection	230V~ 50/60HZ
Electric heater rating in kW	2.76
Total connected load in kW	2.99
Fuse rating in A	13

Dimensions and weight of dryer

External dimensions, height in mm	850
External dimensions, width in mm	596
External dimensions, depth in mm	717
External dimensions, gross height in mm	940
External dimensions, gross width in mm	660
External dimensions, gross depth in mm	820
Net weight in kg	49.0
Gross weight in kg	54
Maximum floor load in N	920

Emissions data

Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	0.76

Features

Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•

Efficiency and sustainability

How it works	Vented
Recycling rate in %	95

Connection options

Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
WiFi	•
WiFiConn@ct	•

Standards, test certificates and symbols

VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•