

DAE 1530 Extractor unit with EasySwitch controls for convenient operation



- Customised kitchen design – fully integrated in 532 mm width
- Powerful – 415 m³/h at the highest level
- LED strip for uniform lighting
- Efficient filtration- 10-ply stainless-steel grease filter
- Safe and easy to clean – Miele CleanCover



EAN: 4002516879633 / Material number: 12760960 /
Old Material Number: 28E1530SGB

General information	
Model identifier	DAE 1530
Manufacturer material number	12760960
EAN number	4002516879633
Marketing class	Silver
Construction type	
Integrated extractor	•
Construction type and design	
Colour	Stainless steel
Operating modes	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 150, DUU 151
Active charcoal filter (order separately)	DKF 32-P
User convenience	
Electronic controls	•
Power levels (number without Booster level)	3
Touch-on-glass controls	•
Controls	EasySwitch
Booster levels	1
Efficiency	
Energy efficiency class (A+++ to D)	B
Annual energy consumption in kWh/year	72.2
Fluid dynamic efficiency class	B
Lighting efficiency class	A
Grease filtering efficiency class	B
Cleaning and care	
Easy-to-clean canopy interior – CleanCover	•
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	1
Lighting	
Number x W	1 x 3,2 W
Light intensity in lx	360 lx
Colour temperature in K	3500 Kelvin
Fan	
Number of fans	1
Dual-action fan	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	215
Air throughput in Level 2 (m ³ /h) according to EN 61591	315
Air throughput in Level 3 (m ³ /h) according to EN 61591	415
Air throughput in Booster level (m ³ /h) according to EN 61591	675
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	45.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	48.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	53.0

DAE 1530
Extractor unit
with EasySwitch controls for convenient operation



EAN: 4002516879633 / Material number: 12760960 /
Old Material Number: 28E1530SGB

Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	65.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	30.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	34.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	39.0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	51.0
Recirculation	
Air throughput in Level 1 (m³/h) according to EN 61591	200
Air throughput in Level 2 (m³/h) according to EN 61591	295
Air throughput in Level 3 (m³/h) according to EN 61591	395
Air throughput in Booster level (m³/h) according to EN 61591	630
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	46.0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	53.0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	59.0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	71.0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	32.0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	39.0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	45.0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	57.0
Safety	
Safety switch-off	•
Technical data	
Canopy width in mm	532
Canopy height in mm	50
Canopy depth in mm	372
Minimum height above electric hobs in mm	450
Minimum height above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Net weight in kg	9.0
Length of supply lead in m	1.5
Standard plug fitted	•
Total rated load in kW	0.20
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Installation notes	
Extraction ducting connection at top	•

DAE 1530
Extractor unit
with EasySwitch controls for convenient operation



EAN: 4002516879633 / Material number: 12760960 /
Old Material Number: 28E1530SGB

Diameter of exhaust duct in mm

150

Accessories included


Non-return flap

•

DAE 1530

Extractor unit

with EasySwitch controls for convenient operation



DAE1530, DAE1535 Installation drawing

1) Exhaust air connection alternatively to the rear., Exhaust air connection Ø 150 mm., Further detailed dimensions can be found in the operating instructions!