

## APCL 107

### Communication box appWash light

for networking washing machines/tumble dryers with appWash PAY and RELAX.



- For use in self-service applications (e.g. laundry/utility rooms)
- Suitable for up to 6 machines (washing machines and dryers)
- Users can book
- Supervisors can use appWash connect to, e.g., view machine utilisation levels
- Find out more about appWash: <https://appwash.com/de/>
- Elec. conn.: 100–240V 50/60Hz – <https://installation.appwash.com/all-languages/>

EAN: 4002516888987 / Material number: 12785910 /

Old Material Number: 59590107EU

| Product category           |   |
|----------------------------|---|
| Washing machines           | • |
| Tumble dryers              | • |
| Ironers                    | • |
| Machine/accessory category |   |
| PM 1210                    | • |
| PM 1214                    | • |
| PM 1217                    | • |
| PRI 318                    | • |
| PRI 418                    | • |
| PRI 210                    | • |
| PRI 214                    | • |
| PRI 217                    | • |
| D 500-1750                 | • |
| PT 5135 C                  | • |
| PT 5136                    | • |
| PT 5137 WP                 | • |
| PT 5186                    | • |
| PT 7186                    | • |
| PT 7188                    | • |
| PT 7135 C                  | • |
| PT 7136                    | • |
| PT 7137 WP                 | • |
| PT 8203                    | • |
| PT 8251                    | • |
| PT 8251 COP                | • |
| PT 8253                    | • |
| PT 8257                    | • |
| PT 8257 WP                 | • |
| PT 8301                    | • |
| PT 8301 COP                | • |
| PT 8303                    | • |
| PT 8331                    | • |
| PT 8331 COP                | • |
| PT 8333                    | • |
| PT 8337                    | • |
| PT 8337 WP                 | • |
| PT 8401                    | • |
| PT 8403                    | • |
| PT 8407                    | • |
| PT 8503                    | • |
| PT 8507                    | • |
| PT 8803                    | • |
| PT 8807                    | • |
| PW 413                     | • |
| PW 418                     | • |
| PW 5065                    | • |
| PW 5082                    | • |

## APCL 107

Communication box appWash light

for networking washing machines/tumble dryers with appWash PAY and RELAX.



EAN: 4002516888987 / Material number: 12785910 /

Old Material Number: 59590107EU

|                   |   |
|-------------------|---|
| PW 5105 Vario     | • |
| PW 6055           | • |
| PW 6065           | • |
| PW 6055 Vario     | • |
| PW 6065 Vario     | • |
| PW 6080           | • |
| PW 6088           | • |
| PW 6107           | • |
| PW 6137           | • |
| PW 5136           | • |
| PW 6167           | • |
| PW 6207           | • |
| PW 811            | • |
| PW 814            | • |
| PW 818            | • |
| PWT 6089          | • |
| PWM 500-08        | • |
| PWM 500-09        | • |
| PWM 507           | • |
| PWM 509           | • |
| PWM 900-09        | • |
| PWM 906           | • |
| PWM 907           | • |
| PWM 908           | • |
| PW 200 Profi@Work | • |
| PT 200 Profi@Work | • |
| PDR 500-08        | • |
| PDR 507           | • |
| PDR 508           | • |
| PDR 900-08        | • |
| PDR 908           | • |
| PWM 511           | • |
| PWM 909           | • |
| PWM 514           | • |
| PWM 520           | • |
| PWM 912           | • |
| PWM 916           | • |
| PWM 920           | • |
| PDW 909           | • |
| PDR 510           | • |
| PDR 511           | • |
| PDR 910           | • |
| PDR 514           | • |
| PDR 516           | • |
| PDR 914           | • |
| PDR 518           | • |
| PDR 918           | • |
| PDR 522           | • |

APCL 107

Communication box appWash light

for networking washing machines/tumble dryers with appWash PAY and RELAX.



EAN: 4002516888987 / Material number: 12785910 /

Old Material Number: 59590107EU

PDR 922

•

## Product category

appWash

•

Payment system

•

## Product properties

Material

Plastic

Colour

Grey

## Dimensions and weight

External dimensions, net height in mm

400

External dimensions, net width in mm

200

External dimensions, net depth in mm

300

External dimensions, gross height in mm

500

External dimensions, gross width in mm

230

External dimensions, gross depth in mm

400

Net weight [kg]

9.00

Gross weight in kg

10.00