

KFN 7934 D

XXL built-in fridge-freezer, 194 cm niche height

DailyFresh I LED I NoFrost I DynaCool I SoftClose



- 45 % more volume in the refrigeration appliance – Built-In XXL
- Spacious drawer with moisture control – DailyFresh
- Optimum and maintenance-free LED lighting in compartment
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance – DynaCool



EAN: 4002516880783 / Material number: 12790400 /
Old Material Number: 38793400EU1

General information	
Model identifier	KFN 7934 D
Manufacturer material number	12790400
EAN number	4002516880783
Marketing class	Gold
Appliance category	
Fridge-freezer	•
Construction type	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
Design	
Refrigeration section lighting	LED
Freezer compartment lighting	LED
User convenience	
Networking with Miele@home	•
Freshness system	DailyFresh
ComfortSize	•
DynaCool	•
NoFrost	•
DuplexCool	•
VarioRoom	•
SoftClose	•
Control system	
Operating concept	TouchControl
SuperCool	•
SuperFreeze	•
No. of temperature zones	2
Sabbath mode	•
Fridge/Fridge section	
No. of shelves	5
No. of crisper drawers	2
Number of inner door racks for tinned food	3
Door rack for bottles	1
Door shelves	4
Freezer/Freezer section	
Number of freezer drawers	3
Efficiency	
Energy efficiency class (A–G)	D
Annual energy consumption in kWh	233.97
Energy consumption in 24 h in kWh	0.56
Safety	
Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Technical data	
Niche width in mm min.	710

KFN 7934 D

XXL built-in fridge-freezer, 194 cm niche height

DailyFresh I LED I NoFrost I DynaCool I SoftClose




EAN: 4002516880783 / Material number: 12790400 /
Old Material Number: 38793400EU1


Niche width in mm max.	718
Niche height in mm min.	1935
Niche height in mm max.	1943
Niche depth in mm	560
Appliance width in mm	708
Appliance height in mm	1935
Appliance depth in mm	548
Weight in kg	72.8
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	20
Max. door front weight – freezer, in kg	19
Climate range	SN-T
Refrigerator compartment in l	284
4* freezer compartment in l	98
Total usable capacity in l	382
Storage time in case of fault in h	13
Freezer capacity in kg/24 h	10.00
Acoustic airborne noise emission class (A–D)	B
Sound emissions in dB(A) re 1 pW	33
Current consumption (mA)	1000
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2.3
Replacing lamps	Service
Accessories included	
Egg tray	•
Water filter	No
Ice cube tray	•

KFN 7934 D

XXL built-in fridge-freezer, 194 cm niche height
DailyFresh I LED I NoFrost I DynaCool I SoftClose




KFN7934D, XXL built-in, side view



KFN7934D, XXL built-in

*The declared energy consumption was calculated in a 560 mm deep niche. The appliance is fully functional in a 550 mm niche but the energy consumption will be slightly higher, **Miele offers various refrigeration appliances with different door gap positions. To increase flexibility for future appliance replacements, we recommend a height of the lower furniture front between 696 and 706 mm. The position of the door gap may shift when replacing the appliance., 1 = 20 kg, 2 = 19 kg



KFN7934D, XXL built-in, installation

1. View from the front, 2. Mains connection cable, L = 2300 mm, 3. Ventilation cut-out min. 200 cm², 4. Ventilation, 5. No connections permitted in this area